

# nVent CADDY Speed Link SLK with Angle Bracket



### **CERTIFICATIONS**







# **FEATURES**

Complete system includes wire, locking device and pre-assembled angle bracket end fitting

Ideal for attaching to concrete, steel or wood surfaces

Simple alternative to jack chain and additional hardware

### **SPECIFICATIONS**

Static Load Safety Factor: 5:

\_. .

Finish: Electrogalvanized

**Material:** Steel;Zinc Alloy;Polypropylene

Complies With: SMACNA HVAC-DCS


| Table 1/2         |                       |                     |       |                |            |           |
|-------------------|-----------------------|---------------------|-------|----------------|------------|-----------|
| Catalog<br>Number | Wire Rope<br>Diameter | Wire Rope<br>Length | A     | Hole Size (HS) | Height (H) | Width (W) |
| SLK15L1AB         | 1.5 mm                | 3.3'                | 0.89" | 0.28"          | 2.15"      | 3/4"      |

| CatalogNumber | Wire Rope<br>Diameter | Wire Rope<br>Length | A     | Hole Size (HS) | Height (H) | Width (W) |
|---------------|-----------------------|---------------------|-------|----------------|------------|-----------|
| SLK15L2AB     | 1.5 mm                | 6.6'                | 0.89" | 0.28"          | 2.15"      | 3/4"      |
| SLK15L3AB     | 1.5 mm                | 9.9'                | 0.89" | 0.28"          | 2.15"      | 3/4"      |
| SLK15L5AB     | 1.5 mm                | 16.4'               | 0.89" | 0.28"          | 2.15"      | 3/4"      |
| SLK2L2AB      | 2 mm                  | 6.6'                | 0.89" | 0.28"          | 2.15"      | 3/4"      |
| SLK2L3AB      | 2 mm                  | 9.9'                | 0.89" | 0.28"          | 2.15"      | 3/4"      |
| SLK2L5AB      | 2 mm                  | 16.4'               | 0.89" | 0.28"          | 2.15"      | 3/4"      |
| SLK3L10AB     | 3 mm                  | 32.8'               | 0.89" | 0.28"          | 2 1/2"     | 0.9"      |
| SLK3L5AB      | 3 mm                  | 16.4'               | 0.89" | 0.28"          | 2 1/2"     | 0.9"      |
| SLK3L7AB      | 3 mm                  | 22.9'               | 0.89" | 0.28"          | 2 1/2"     | 0.9"      |


| Table 2/2      |               |           |                 |                |  |
|----------------|---------------|-----------|-----------------|----------------|--|
| Catalog Number | Thickness (T) | Angle (a) | Static Load (F) | Certifications |  |
| SLK15L1AB      | 1/2"          | 90 ° Max  | 44lbf           | ITB, UL, cUL   |  |
| SLK15L2AB      | 1/2"          | 90 ° Max  | 44lbf           | ITB, UL, cUL   |  |
| SLK15L3AB      | 1/2"          | 90 ° Max  | 44lbf           | cUL, ITB, UL   |  |
| SLK15L5AB      | 1/2"          | 90 ° Max  | 44lbf           | ITB, UL, cUL   |  |
| SLK2L2AB       | 1/2"          | 90 ° Max  | 100lbf          | ITB, UL, cUL   |  |
| SLK2L3AB       | 1/2"          | 90 ° Max  | 100lbf          | ITB, UL, cUL   |  |
| SLK2L5AB       | 1/2"          | 90 ° Max  | 100lbf          | ITB, UL, cUL   |  |
| SLK3L10AB      | 0.6"          | 90 ° Max  | 200lbf          |                |  |

| Catalog Number | Thickness (T) | Angle (a) | Static Load (F) | Certifications |
|----------------|---------------|-----------|-----------------|----------------|
| SLK3L5AB       | 0.6"          | 90 ° Max  | 200lbf          |                |
| SLK3L7AB       | 0.6"          | 90 ° Max  | 200lbf          |                |

# **DIAGRAMS**







## **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### **North America**

+1.800.753.9221 Option 1 - Customer Care Option 2 - Technical Support

### Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

### Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

# **APAC**

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

**CADDY** 

**ERICO** 

**HOFFMAN** 

**ILSCO SCHROFF**  **TRACHTE** 

