

nVent CADDY Speed Link SLK with Hook



CERTIFICATIONS



FEATURES

Complete system includes wire, locking device and pre-assembled hook end fitting

Hooks to a wide range of nVent CADDY fasteners

Fastens to the building structure or hanging services by looping around and hooking to wire rope

Easy to remove for applications requiring maintenance

Spring latch helps provide secure connection

Insert cable through hole and use bottom side of hook as an end stop

Also available in Y-hook configuration

SPECIFICATIONS

Static Load Safety Factor:	5:1
Finish:	Electrogalvanized
Material:	Steel; Polypropylene; Zinc Alloy
Complies With:	SMACNA HVAC-DCS

Table 1/2

Catalog Number	Wire Rope Diameter	Wire Rope Length	A	B	C	Height (H)
----------------	--------------------	------------------	---	---	---	------------


SLK15L1	1.5 mm	3.3'	1.89"	0.71"	0.18"	2.15"
SLK15L10	1.5 mm	32.8'	1.89"	0.71"	0.18"	2.15"
SLK15L2	1.5 mm	6.6'	1.89"	0.71"	0.18"	2.15"
SLK15L2R2	1.5 mm	6.6'	1.89"	0.71"	0.18"	2.15"
SLK15L3	1.5 mm	9.9'	1.89"	0.71"	0.18"	2.15"
SLK15L3R2	1.5 mm	9.9'	1.89"	0.71"	0.18"	2.15"
SLK15L5	1.5 mm	16.4'	1.89"	0.71"	0.18"	2.15"
SLK15L5R2	1.5 mm	16.4'	1.89"	0.71"	0.18"	2.15"
SLK2L1	2 mm	3.3'	2.24"	0.87"	0.22"	2.15"
SLK2L10	2 mm	32.8'	2.24"	0.87"	0.22"	2.15"
SLK2L2	2 mm	6.6'	2.24"	0.87"	0.22"	2.15"
SLK2L2R2	2 mm	6.6'	2.24"	0.87"	0.22"	2.15"
SLK2L3	2 mm	9.9'	2.24"	0.87"	0.22"	2.15"
SLK2L3R2	2 mm	9.9'	2.24"	0.87"	0.22"	2.15"
SLK2L5	2 mm	16.4'	2.24"	0.87"	0.22"	2.15"
SLK3L1	3 mm	3.3'	2.27"	0.91"	0.24"	2 1/2"
SLK3L10	3 mm	32.8'	2.27"	0.91"	0.24"	2 1/2"
SLK3L2	3 mm	6.6'	2.27"	0.91"	0.24"	2 1/2"
SLK3L3	3 mm	9.9'	2.27"	0.91"	0.24"	2 1/2"

SLK3L3R2	3 mm	9.9'	2.27"	0.91"	0.24"	2 1/2"
SLK3L5	3 mm	16.4'	2.27"	0.91"	0.24"	2 1/2"
SLK3L5R2	3 mm	16.4'	2.27"	0.91"	0.24"	2 1/2"

Table 2/2					
Catalog Number	Width (W)	Thickness (T)	Angle (a)	Static Load (F)	Certifications
SLK15L1	3/4"	1/2"	90 ° Max	44lbf	UL, cUL, SMACNA
SLK15L10	3/4"	1/2"	90 ° Max	44lbf	SMACNA, UL, cUL
SLK15L2	3/4"	1/2"	90 ° Max	44lbf	SMACNA, UL, cUL
SLK15L2R2	3/4"	1/2"	90 ° Max	44lbf	SMACNA, UL, cUL
SLK15L3	3/4"	1/2"	90 ° Max	44lbf	UL, cUL, SMACNA
SLK15L3R2	3/4"	1/2"	90 ° Max	44lbf	UL, cUL, SMACNA
SLK15L5	3/4"	1/2"	90 ° Max	44lbf	SMACNA, UL, cUL
SLK15L5R2	3/4"	1/2"	90 ° Max	44lbf	UL, cUL, SMACNA
SLK2L1	3/4"	1/2"	90 ° Max	100lbf	SMACNA, UL, cUL
SLK2L10	3/4"	1/2"	90 ° Max	100lbf	SMACNA, UL, cUL
SLK2L2	3/4"	1/2"	90 ° Max	100lbf	UL, cUL, SMACNA
SLK2L2R2	3/4"	1/2"	90 ° Max	100lbf	UL, cUL, SMACNA
SLK2L3	3/4"	1/2"	90 ° Max	100lbf	SMACNA, UL, cUL
SLK2L3R2	3/4"	1/2"	90 ° Max	100lbf	SMACNA, UL, cUL
SLK2L5	3/4"	1/2"	90 ° Max	100lbf	UL, cUL, SMACNA

Catalog Number	Width (W)	Thickness (T)	Angle (a)	Static Load (F)	Certifications
SLK3L1	0.9"	0.6"	90 ° Max	200lbf	SMACNA
SLK3L10	0.9"	0.6"	90 ° Max	200lbf	SMACNA
SLK3L2	0.9"	0.6"	90 ° Max	200lbf	SMACNA
SLK3L3	0.9"	0.6"	90 ° Max	200lbf	SMACNA
SLK3L3R2	0.9"	0.6"	90 ° Max	200lbf	SMACNA
SLK3L5	0.9"	0.6"	90 ° Max	200lbf	SMACNA
SLK3L5R2	0.9"	0.6"	90 ° Max	200lbf	SMACNA

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

