

# nVent CADDY Superklip



## FEATURES

Closes and locks automatically when the pipe, tube or cable is inserted

One-piece clamp for fast and convenient installation

Fasten with either wood screw, dual threaded screw with or without collar, nail with collar, threaded rod, mounting plate or shot-fire bracket

## SPECIFICATIONS

**Material:** Xenoy®

**Temperature:** -13 to 194 °F

Table 1/2

Catalog Number	Outer Diameter (OD)	Rigid Conduit Size	Pipe Size	Copper Tube Size	B	C
389017	0.310" - 0.37"			1/4"	11/16"	11/16"
389018	0.370" - 0.46"			1/4"	11/16"	11/16"
389003	0.660" - 0.77"	3/8"	3/8"	5/8"	5/8"	1 13/32"
389001	0.460" - 0.56"			3/8"	9/16"	1 3/16"
389004	0.770" - 0.86"	1/2"	1/2"		5/8"	1 9/16"


CatalogNumber	Outer Diameter (OD)	Rigid Conduit Size	Pipe Size	Copper Tube Size	B	C
389002	0.560" - 0.66"			1/2"	9/16"	1 3/16"
389005	0.860" - 0.98"			3/4"	21/32"	1 5/8"
389006	0.980" - 1.09"	3/4"	3/4"		11/16"	1 3/4"
389007	1.090" - 1.23"			1"	11/16"	1 15/16"
389008	1.230" - 1.4"	1"	1"	1 1/4"	11/16"	2 1/8"
389009	1.400" - 1.56"			1 1/4"	11/16"	2 5/16"
389011	1.560" - 1.71"	1 1/4"	1 1/4" Min	1 1/2"	3/4"	2 1/2"
389012	1.83" - 2"	1 1/2"	1 1/2"		3/4"	2 7/8"
389013	2.000" - 2.19"			2"	25/32"	3 3/32"
389014	2.300" - 2.52"	2"	2" Min		13/16"	3 15/32"

Table 2/2

Catalog Number	Static Load (F)
389017	30lbf
389018	33lbf
389003	43lbf
389001	35lbf
389004	50lbf
389002	40lbf
389005	48lbf

Catalog Number	Static Load (F)
389006	54lbf
389007	58lbf
389008	67lbf
389009	72lbf
389011	80lbf
389012	84lbf
389013	90lbf
389014	92lbf

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**

