

# nVent CADDY Swift Clip Threaded Rod Attachment



## **FEATURES**

Snap-on and twist installation requires no tools

Easily adjusts by rotating up or down on the threaded rod

For support and positioning of refrigeration, A/C tubing, PEX piping, conduit and cabling

Secures pipe and insulation without any breaks

Compliant with UL® 2043 and suitable for use in air handling (plenum) spaces

# **SPECIFICATIONS**

Material: Polyamide
Working Temperature: -40 to 284 °F

Table 1/1						
Catalog Number	Outer Diameter	Copper Tube Size	Pipe Size	Rod Size		
TRC212	2 1/8"	2"		3/8"		
TRC162	1 5/8"	1 1/2"		3/8"		
TRC125	1 1/4"		1"	3/8"		
TRC137	1 3/8"	1 1/4"		3/8"		

Catalog Number	Outer Diameter	Copper Tube Size	Pipe Size	Rod Size
TRC112	1 1/8"	1"		3/8"
TRC100	1"		3/4"	3/8"
TRC200	2"			3/8"
TRC087	7/8"	3/4"	1/2"	3/8"
TRC150	1 1/2"			3/8"
TRC075	3/4"	5/8"		3/8"
TRC062	5/8"	1/2"		3/8"

## ADDITIONAL PRODUCT DETAILS

Clip must be installed with temperature at or above 14 °F (-10 °C).

## **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### **North America**

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

# Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

#### Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

#### **APAC**

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

**CADDY** 

**ERICO** 

**HOFFMAN** 

ILSCO SCHROFF

TRACHTE

