

nVent CADDY Swift Clip Threaded Rod Attachment



FEATURES

Snap-on and twist installation requires no tools

Easily adjusts by rotating up or down on the threaded rod

For support and positioning of refrigeration, A/C tubing, PEX piping, conduit and cabling

Secures pipe and insulation without any breaks

Compliant with UL® 2043 and suitable for use in air handling (plenum) spaces

SPECIFICATIONS

Material: Polyamide

Working Temperature: -40 to 284 °F

Table 1/1

Catalog Number	Outer Diameter	Copper Tube Size	Pipe Size	Rod Size
TRC062	5/8"	1/2"		3/8"
TRC075	3/4"	5/8"		3/8"
TRC087	7/8"	3/4"	1/2"	3/8"
TRC100	1"		3/4"	3/8"

Catalog Number	Outer Diameter	Copper Tube Size	Pipe Size	Rod Size
TRC112	1 1/8"	1"		3/8"
TRC125	1 1/4"		1"	3/8"
TRC137	1 3/8"	1 1/4"		3/8"
TRC150	1 1/2"			3/8"
TRC162	1 5/8"	1 1/2"		3/8"
TRC200	2"			3/8"
TRC212	2 1/8"	2"		3/8"

ADDITIONAL PRODUCT DETAILS

Clip must be installed with temperature at or above 14 °F (-10 °C).

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

