

## nVent CADDY Telescoping Rigid Box Support Bracket Between Stud Assembly



## **FEATURES**

Accommodates up to 6-gang box in 16" stud spacing or up to 10-gang in 24" stud spacing

Open design allows a variety of positions for box location

Easy to adjust after the electrical box is installed

## **SPECIFICATIONS**

**Knockout Sizes, Box 2:** (12) 1/2", 3/4"

**Knockout Sizes, Box 1:** (4) 1/2", 3/4";(8) 1/2"

Finish: Pregalvanized

Material: Steel

Table 1/2							
Catalog Number	Box Depth	Box Size 1	Box Size 2	Drywall Thickness	Gang, Box 1	Gang, Box 2	
TR4DM1P1M5	2.12"	4"	4 11/16"	3/4"	1	1	
TR4DM1	2.12"	4"		3/4"	1		

Table 2/2						
Catalog Number	Ground Wire ncluded	Mud Ring Type	Stud Spacing	Volume, Box 1	Volume, Box 2	

TR4DM1P1M5	Yes	Raised	16" - 24"	30.3in³	42in³	
TR4DM1	Yes	Raised	16" - 24"	30.3in³		

## **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America** 

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support Europe

Netherlands: +31 800-0200135 France: +33 800 901 793 Europe

Germany: 800 1890272 Other Countries: +31 13 5835404 APAC

Shanghai: + 86 21 2412 1618/19 Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY** 

**ERICO** 

**HOFFMAN** 

**ILSCO** 

**SCHROFF** 

**TRACHTE** 



©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.