


# **Oval Sleeve**



The nVent CADDY Oval Sleeve is a fast and effective way to secure cable to rooftop equipment. By utilizing the nVent CADDY Manual Swaging Tool, contractors working on rooftops or in the shop can now benefit from a full-service solution designed for durability and longevity throughout high and low temperatures. Made to secure various rooftop equipment such as metal ducts, HVAC units, piping and walkways.

## **CERTIFICATIONS**





#### **FEATURES**

Designed to be used exclusively with size 3/16 stainless steel nVent CADDY Pyramid Rooftop Anchor Cable Bracing and nVent CADDY Manual Swaging Tool

Versatile solution designed for on-site and in-shop use

Stainless steel is corrosion and harsh weather-resistant

## **SPECIFICATIONS**

Material: Copper

Finish: Electrogalvanized

Table 1/1	
Catalog Number	Brace Size
CSB12SLVB	#12
CSB18SLVB	#18
CSB36SLVB	#36

### **ADDITIONAL PRODUCT DETAILS**

Two side-by-side swages required on #12 and #18 cable. Three side-by-side swages required on #36 and #48 cable.

Check swage with gauge (not included).

#### **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### **North America**

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

# Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

#### Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

# APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

**CADDY** 

**ERICO** 

**HOFFMAN** 

**ILSCO** 

**SCHROFF** 

TRACHTE

