

Push In Conduit Clamp



FEATURES

Push-in installation of conduit

Eliminates need for offset bending conduit

May be used for either vertical or horizontal installations

SPECIFICATIONS


Finish: nVent CADDY Armour


Material: Spring Steel

Table 1/1										
Catalog Number	EMT Conduit Size	Outer Diameter (OD)	Hole Size (HS)	Hole Type	Ultimate Static Load 1 (F1)	Ultimate Static Load 2 (F2)				
16P4I	1"	1"	1/4"	Threaded	25lb	15lb				
8P4I	1/2"	0.710" - 0.87"	1/4"	Threaded	25lb	15lb				
12P4I	3/4"	3/4"	1/4"	Threaded	25lb	15lb				
16P	1"	1.180" - 1.38"	9/32"	Plain	25lb	15lb				
12P	3/4"	0.870" - 1.18"	9/32"	Plain	25lb	15lb				

CatalogNumber	EMT Conduit Size	Outer Diameter (OD)	Hole Size (HS)	Hole Type	Ultimate Static Load 1 (F1)	Ultimate Static Load 2 (F2)
8P	1/2"	0.710" - 0.87"	9/32"	Plain	25lb	15lb

DIAGRAMS





WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN IL

ILSCO SCHROFF

TRACHTE



nVent.com/CADDY 2

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.