

Push In Conduit to Rod/Wire Clip



FEATURES

Provides attachment of conduit and boxes

Increased capability and application options by combining 4Z and 6Z products into one enhanced and efficient offering

Improved multi-function clip allows for optimized inventory while reducing job site scheduling risks associated with multiple SKUs

SPECIFICATIONS

Finish: nVent CADDY Armour

Material: Spring Steel

Table 1/1

Catalog Number	EMT Conduit Size	Rigid Conduit Size	Outer Diameter	Rod Size	Wire Size	Flange Thickness
4Z348P	1/2"		1/2"	1/4", 5/16", 3/8"	#12 - #8	1/8" - 3/8"
4Z3412P	3/4"	1/2"	3/4"	1/4", 5/16", 3/8"	#12 - #8	1/8" - 3/8"
4Z3416P	1"	3/4"	1"	1/4", 5/16", 3/8"	#12 - #8	1/8" - 3/8"

ADDITIONAL PRODUCT DETAILS

NEC® 300.11 requires dedicated drop wire/rod and EC311.

4Z parts installed on 3/8" (M10) smooth rod in the F2 direction has a Static Load Rating of 15 lb (67 N).

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

