

Quick Grip Jr. Lateral Sway Brace



CERTIFICATIONS









FEATURES

Easy two-step installation eliminates extra trips between structure and service pipe

Works with 1" and 1 1/4" (25 mm and 32 mm) brace pipes to reduce inventory

Snap-off bolt head helps enable easy installation and inspection of seismic sway braces

Meets NFPA®-13 requirements for seismic sway bracing

Meets CEN/TS 17551:2021 requirements for Seismic Sway Bracing

SPECIFICATIONS

Finish: Electrogalvanized


Material: Steel

Table 1/1					
Catalog Number	Pipe Size	Height (H)	Width (W)		
CSBQIKCL0100EG	1"	5 1/8"	2 5/8"		
CSBQIKCL0150EG	1 1/2"	5 5/8"	3 1/4"		

Catalog Number	Pipe Size	Height (H)	Width (W)
CSBQIKCL0125EG	1 1/4"	5 3/8"	3"
CSBQIKCL0200EG	2"	6 3/8"	3 5/8"

UL Loads (Listed for Restraints)				
Part Number	Service Pipe Schedule	Lateral		
		1" Brace Pipe	1 1/4" Brace Pipe	
CSBQIKCL0100EG	Dyna-Flow®	N/A	N/A	
	10	655 lb	655 lb	
	40	655 lb	655 lb	
CSBQIKCL0125EG	Dyna-Flow®	655 lb	540 lb	
	10	655 lb	540 lb	
	40	655 lb	540 lb	
CSBQIKCL0150EG	Dyna-Flow®	750 lb	655 lb	
	10	750 lb	655 lb	
	40	750 lb	655 lb	
CSBQIKCL0200EG	Dyna-Flow®	750 lb	540 lb	
	10	750 lb	540 lb	
	40	750 lb	540 lb	

FM Loads						
Part Number	Service Pipe Schedule	Lateral				
		Horizontal Capacity per Installation Angle from Vertical				
		30°- 44°	45°- 59°	60°- 74°	75°- 90°	
CSBQIKCL0100EG	Lightwall	290 lb	410 lb	495 lb	550 lb	
	10	150 lb	210 lb	280 lb	315 lb	
	40	475 lb	665 lb	825 lb	925 lb	
CSBQIKCL0125EG	Lightwall	290 lb	410 lb	495 lb	550 lb	
	10	150 lb	210 lb	280 lb	315 lb	
	40	475 lb	665 lb	825 lb	925 lb	
CSBQIKCL0150EG	Lightwall	290 lb	410 lb	495 lb	550 lb	
	10	150 lb	210 lb	280 lb	315 lb	
	40	475 lb	665 lb	825 lb	925 lb	
CSBQIKCL0200EG	Lightwall	390 lb	550 lb	670 lb	750 lb	
	10	350 lb	500 lb	620 lb	690 lb	
	40	490 lb	690 lb	850 lb	950 lb	





WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO SCHROFF

TRACHTE

