

# **Quick Grip Lateral Sway Brace**



The Quick Grip Lateral Brace, part of the nVent CADDY line of fire sprinkler bracing systems from nVent, is designed to help simplify installations when bracing service pipe for seismic or other catastrophic events. It features an innovative design for quick attachment of brace pipe to service pipe saving time and money.

#### CERTIFICATIONS











#### **FEATURES**

Easy two-step installation eliminates extra trips between structure and service pipe

Works with 1" and 1 1/4" (25 mm and 32 mm) brace pipes to reduce inventory

Yellow tips provide a visual indicator that the bolts have been properly torqued

Easy installation with an impact wrench from the bottom side of the clamp

Meets NFPA®-13 requirements for seismic sway bracing

Meets CEN/TS 17551:2021 requirements for Seismic Sway Bracing

#### **SPECIFICATIONS**

Finish: Electrogalvanized

Material: Steel


Table 1/1				
Catalog Number	Pipe Size	Height (H)	Width (W)	Certifications
CSBQG0250EG	2 1/2"	5 7/16" - 5 7/8"	6 3/4"	OSHPD, UL, FM Approved, Seismic, cUL

Catalog Number	Pipe Size	Height (H)	Width (W)	Certifications
CSBQG0300EG	3"	6 1/8" - 6 1/2"	7 1/2"	AON Fire Protection, Rigid Seismic, OSHPD, UL, FM Approved, Seismic, cUL
CSBQG0400EG	4"	7 1/8" - 7 1/2"	8 3/4"	OSHPD/HCAI, UL, FM Approved, Seismic, AON Fire Protection, Rigid Seismic, cUL
CSBQG0600EG	6"	9 1/4" - 9 5/8"	11 3/4"	cUL, UL, FM Approved, Seismic, OSHPD/HCAI, AON Fire Protection, Rigid Seismic
CSBQG0800EG	8"	11 3/8" - 11 13/16"	13 7/8"	AON Fire Protection, Rigid Seismic, OSHPD, UL, FM Approved, Seismic, cUL

UL Loads					
Part Number	Lateral				
	Sch 10/Sch 40 Service Pipe	Bull Moose Eddy Flow Service Pipe	Wheatland Mega-Flow Service Pipe	Youngstown Fire-Flo Service Pipe	
CSBQG0250	1500 lb	1500 lb	1500 lb	1500 lb	
CSBQG0300	1300 lb	1300 lb	1300 lb	1300 lb	
CSBQG0400	1500 lb	1500 lb	1500 lb	1500 lb	
CSBQG0500	N/A	N/A	N/A	N/A	
CSBQG0600	1400 lb	N/A	1400 lb	N/A	
CSBQG0800	1400 lb	N/A	N/A	N/A	

FM Loads						
		Lateral	Lateral  Horizontal Capacity per Installation Angle from Vertical			
Part Number	Service Pipe Schedule	Horizontal Capa				
		30°- 44°	45°- 59°	60°- 74°	75°- 90°	
CSBQG0250EG	Lightwall	1,410 lb	2,000 lb	2,450 lb	2,740 lb	
	10	1,410 lb	2,000 lb	2,450 lb	2,740 lb	
	40	1,410 lb	2,000 lb	2,450 lb	2,740 lb	
CSBQG0300EG	Lightwall	1,190 lb	1,680 lb	2,060 lb	2,300 lb	
	10	1,190 lb	1,680 lb	2,060 lb	2,300 lb	
	40	1,190 lb	1,680 lb	2,060 lb	2,300 lb	
CSBQG0400EG	Lightwall	1,190 lb	1,680 lb	2,060 lb	2,300 lb	
	10	1,190 lb	1,680 lb	2,060 lb	2,300 lb	
	40	1,190 lb	1,680 lb	2,060 lb	2,300 lb	
CSBQG0600EG	Lightwall	870 lb	1,230 lb	1,510 lb	1,690 lb	
	10	870 lb	1,230 lb	1,510 lb	1,690 lb	
	40	970 lb	1,370 lb	1,680 lb	1,870 lb	
CSBQG0800EG	0.188" (Wall Thickness)	790 lb	1,110 lb	1,360 lb	1,520 lb	
	40	790 lb	1,110 lb	1,360 lb	1,520 lb	

### **DIAGRAMS**





#### **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

## North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

## Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

#### **Europe**

Germany: 800 1890272 Other Countries: +31 13 5835404

#### **APAC**

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY

**ERICO** 

**HOFFMAN** 

**ILSCO** 

**SCHROFF** 

**TRACHTE** 

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.