

SBT Multiple Conduit Mounting Plate



FEATURES

Single point structure attachment and easy "snap-in" field assembly of up to three conduit clips

No tools necessary for installation of clips (box size - 4")

Eliminates need for offset bending conduit

Available in a variety of riveted assemblies

Helps eliminate multiple beam clamps or strut assemblies

SPECIFICATIONS

Finish: nVent CADDY Armour

Material: Spring Steel

Table 1/1

Catalog Number	Static Load
SBT18	150lb
SBT18TI	150lb

ADDITIONAL PRODUCT DETAILS

TI letters in the part number stands for "Thread Impression"

Static Load represents the maximum load limit of the assembly. Static load limit of each locking tab is 50 lb (220 N). The combined loads of the locking tabs shall not exceed the maximum load limit of the assembly.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

