

SBT-Z Multiple Conduit Mounting Plate with Rod/Wire Clip



CERTIFICATIONS



BABA

FEATURES

Single point structure attachment and easy "snap-in" field assembly of up to three conduit clips

No tools necessary for installation of clips (box size - 4")

Eliminates need for offset bending conduit

Helps eliminate multiple beam clamps or strut assemblies

Increased capability and application options by combining 4Z and 6Z products into one enhanced and efficient offering

Improved multi-function clip allows for optimized inventory while reducing job site scheduling risks associated with multiple SKUs

SPECIFICATIONS

Table 1/1

Catalog Number	Material	Finish	Flange Thickness	Rod Size	Wire Size	Static Load
SBT184Z34	Spring Steel	nVent CADDY Armour	0.1250" - 0.4375"	1/4", 5/16", 3/8"	#12 - #8	20lb

ADDITIONAL PRODUCT DETAILS

Static Load represents the maximum load limit of the assembly.

4Z parts installed on 3/8" (M10) smooth rod in the F2 direction has a Static Load Rating of 15 lb (67 N).

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

