

# Snap Close Conduit to Conduit Clamp



## CERTIFICATIONS



## FEATURES

Fast and easy assembly for lightweight loads

No screws or bolts required

## SPECIFICATIONS

**Finish:** nVent CADDY Armour

**Material:** Spring Steel

Table 1/2

Catalog Number	EMT Conduit Size 1	EMT Conduit Size 2	Flexible Conduit Size	MC/AC Cable Size	Outer Diameter 1	Outer Diameter 2
166M	3/4", 1"	3/8"	3/8"	14-2 to 12-3	0.920" - 1.38"	0.550" - 0.71"
1616M	3/4", 1"	3/4", 1"			0.920" - 1.38"	0.920" - 1.38"

Table 2/2

Catalog Number	Ultimate Static Load	Certifications
----------------	----------------------	----------------

166M	100lb	
1616M	100lb	UL, cUL

ADDITIONAL PRODUCT DETAILS

For 14-2 through 12-3 MC/AC cable, use part 166M.

Total load of trapeze must not exceed 100 lb.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

