

Strut Beam Clamp with U-Bolt



FEATURES

Complete with U-bolt and nuts

Requires installation in pairs

SPECIFICATIONS

Finish: Electrogalvanized


Material: Steel


Table 1/2								
Catalog Number	Strut Type	Rod Size (RS)	Flange Thickness (FT)	Width (W)	Thickness (T)	A		
BC17D000EG	AA (3 1/4" x 1 5/8"), D (2 7/16" x 1 5/8"), E (3 1/4" x 1 5/8")	3/8"	13/16" Max	3"	1/4"	11/16"		
BC17A000EG	A (1 5/8" x 1 5/8"), C (13/16" x 1 5/8")	3/8"	13/16" Max	3"	1/4"	11/16"		

Table 2/2							
Catalog Number	В	С	Static Load (F)				
BC17D000EG	1 11/16"	5"	1200lbf				
BC17A000EG	1 11/16"	3 3/8"	1200lbf				

Static Load is based on one pair of Strut Beam Clamps.

DIAGRAMS





WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 - Customer Care Option 2 - Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

