

Telescoping Plumbing Bracket



CERTIFICATIONS



FEATURES

Notched and marked for easy identification and bending

Adjustable for non-standard stud spacing

Interlocking tab prevents accidental disassembly

Can be mounted at multiple depths to face or inside of stud

Additional pilot holes in bracket allow for easy attachment utilizing multiple standard solutions

Increased rigidity for heavier-duty plumbing applications

Requires only a screw gun to install

SPECIFICATIONS

Table 1/1

Catalog Number	Material	Finish	Stud Spacing
TPB1624	Steel	Pregalvanized	15 3/4" - 25"

Bend Lines	
Center of Stud	1 13/16"
In Stud Cavity	2 1/2"
Back of Stud	3 1/4"

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

