

Threaded Bridle Ring



CERTIFICATIONS



FEATURES

Combine bridle rings with other nVent CADDY fasteners to support cables from flange, purlin, drop wire, t-grid, etc.

SPECIFICATIONS

Finish: Electrogalvanized

Material: Steel

Table 1/1

Catalog Number	Diameter	Screw Diameter	Screw Type	Screw Length	Ultimate Static Load	Certifications
4BRT20	1 1/4"	1/4"	Metal	1/2"	50lb	UL, cUL
4BRT32	2"	1/4"	Metal	1/2"	50lb	cUL, UL
4BRT64	4"	1/4"	Metal	1/2"	50lb	cUL, UL
2BRT8	1/2"	10"	Metal	1/2"	50lb	UL, cUL

CatalogNumber	Diameter	ScrewDiameter	Screw Type	Screw Length	Ultimate Static Load	Certifications
2BRT20	1 1/4"	10"	Metal	1/2"	50lb	UL, cUL
2BRT32	2"	10"	Metal	1/2"	50lb	cUL, UL
4BRT20WS	1 1/4"	0.55"	Wood	3/4"	50lb	UL, cUL
4BRT32WS	2"	14"	Wood	3/4"	50lb	UL, ITB, cUL

ADDITIONAL PRODUCT DETAILS

Bridle Rings not recommended for high performance cables. See nVent CADDY Cat HP J-Hook System.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

