

Universal Restraint Clip



CERTIFICATIONS











FEATURES

Attaches cable brace to structure

Meets CEN/TS 17551:2021 requirements for Seismic Sway Bracing

SPECIFICATIONS

Table 1/2						
Catalog Number	Material	Finish	Brace Size	Hole Size (HS)	Thickness (T)	UL Listed Load
CSBURC38SS	Stainless Steel 316 (EN 1.4401)		#12, #18, #36	7/16"	0.17"	618lb
CSBURC38	Steel	Electrogalvaniz ed	#12, #18, #36	7/16"	0.17"	771lb
CSBURC58SS	Stainless Steel 316 (EN 1.4401)		#12, #18, #36	11/16"	0.17"	618lb
CSBURC58	Steel	Electrogalvaniz ed	#12, #18, #36	11/16"	0.17"	771lb

CatalogNumber	Material	Finish	Brace Size	Hole Size (HS)	Thickness (T)	UL Listed Load
CSBURC12SS	Stainless Steel 316 (EN 1.4401)		#12, #18, #36	9/16"	0.17"	618lb
CSBURC12	Steel	Electrogalvaniz ed	#12, #18, #36	9/16"	0.17"	771lb


Table 2/2				
Catalog Number	Certifications			
CSBURC38SS				
CSBURC38	OSHPD/HCAI, UL, cUL, ICC-ES (Seismic Cable Bracing), ICC-ES			
CSBURC58SS				
CSBURC58	ICC-ES (Seismic Cable Bracing), ICC-ES, UL, cUL, OSHPD/HCAI			
CSBURC12SS				
CSBURC12	ICC-ES (Seismic Cable Bracing), ICC-ES, OSHPD/HCAI, UL, cUL			

ADDITIONAL PRODUCT DETAILS

Brace member is not included.

Mount to the structure using the center hole. Loop cable through the holes in the bent tabs and swage in place.

UL Loads				
Part Number	Brace Member	Load Rating		
	CSB12CBL	418 lb		
CSBURC38	CSB18CBL	772 lb		
	CSB36CBL	1909 lb		
	CSB12CBL	418 lb		
CSBURC12	CSB18CBL	772 lb		
	CSB36CBL	1909 lb		
	CSB12CBL	418 lb		
CSBURC58	CSB18CBL	772 lb		
	CSB36CBL	1909 lb		



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

