

# WBT Performance Cable Tray C Bracket



Engineered for efficiency and adaptability, the nVent CADDY WBT Performance Cable Tray C Bracket is a fast and simple component of modern cable management systems.

Designed to streamline installation processes, this bracket excels in both hard-ceiling and two-tier wall mounting scenarios, offering contractors a reliable and time-saving solution for complex environments

The C Bracket ensures that high-performance, low-voltage and data cables are securely supported with minimal effort. Simply pair with the nVent CADDY WBT Performance Cable Tray Washer Support or nVent CADDY WBT Performance Cable Tray Ground Splice and quickly fasten it to the wire basket tray to create a robust framework for layered tray runs. This combination not only enhances structural integrity but also provides the flexibility needed for multi-tiered installations, accommodating evolving infrastructure demands without compromising safety or performance

## FEATURES

Easy-to-use quick connect feature

Designed to be used with the nVent CADDY WBT Performance Cable Tray Washer Support and nVent CADDY WBT Performance Cable Tray Ground Splice

Side load access for cable installation

Ideal for ceiling, wall and channel installations

Side load access for simple cable installation

## SPECIFICATIONS

**Finish:** Electrogalvanized

**Material:** Steel

Table 1/1

Catalog Number	Color	Height	Width	Length	Hole Size	Unit Weight
WBTCBRKT12		5 1/2"	7 7/8"	13.8"	0.281"	4 lb

CatalogNumber	Color	Height	Width	Length	Hole Size	Unit Weight
WBTCBRKT12B A	Black	5 1/2"	7 7/8"	13.8"	0.281"	4 lb
WBTCBRKT12 WH	White	5 1/2"	7 7/8"	13.8"	0.281"	4 lb
WBTCBRKT18		5 1/2"	7 7/8"	19.65"	0.281"	4 lb
WBTCBRKT18B A	Black	5 1/2"	7 7/8"	19.65"	0.281"	4 lb
WBTCBRKT18 WH	White	5 1/2"	7 7/8"	19.65"	0.281"	4 lb
WBTCBRKT4		5 1/2"	7 7/8"	5.981"	0.281"	2 lb
WBTCBRKT4BA	Black	5 1/2"	7 7/8"	5.981"	0.281"	2 lb
WBTCBRKT6		5 1/2"	7 7/8"	7.95"	0.281"	2 lb
WBTCBRKT6BA	Black	5 1/2"	7 7/8"	7.95"	0.281"	2 lb
WBTCBRKT8		5 1/2"	7 7/8"	9.9"	0.281"	2 lb
WBTCBRKT8BA	Black	5 1/2"	7 7/8"	9.9"	0.281"	2 lb

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**

