

WBT Performance Cable Tray Ceiling Support



In the evolving landscape of cable management, the nVent CADDY WBT Performance Tray Ceiling Support is a simple and efficient alternative to traditional strut trapeze systems for wire basket tray installations. Engineered for simplicity and strength, this support solution not only anchors wire basket trays securely to the ceiling but also doubles as a splice point—making it a dual-function component that enhances both structural integrity and installation efficiency.

Compatible with varying nVent CADDY WBT Performance Cable Tray sizes, the ceiling support is precision-engineered to handle the weight of the trays with confidence. Its prepunched design simplifies mounting with standard fasteners. Its compatibility with various finishes—including pre-galvanized, zinc electroplate, and powder coat options—adds aesthetic and functional versatility to any project.

FEATURES

Use as a center support or support provisioned from both ends

Designed to be used with the nVent CADDY WBT Performance Cable Tray Ground Splice and nVent CADDY WBT Performance Cable Tray Splice Kit

Supported with 3/8 or ½ in threaded rod

SPECIFICATIONS

Material: Steel

Table 1/2						
Catalog Number	Finish	Color	Height	Width	Length	Hole Size 1
WBTCLSPRT12	Electrogalvaniz ed		0.62"	1.63"	15.292"	0.281"
WBTCLSPRT12 BA	Electrogalvaniz ed	Black	0.62"	1.63"	15.292"	0.281"

CatalogNumber	Finish	Color	Height	Width	Length	Hole Size 1
WBTCLSPRT12 WH	Electrogalvaniz ed	White	0.62"	1.63"	15.292"	0.281"
WBTCLSPRT16	Pregalvanized		0.62"	1.63"	19.229"	0.281"
WBTCLSPRT16 BA	Pregalvanized	Black	0.62"	1.63"	19.229"	0.281"
WBTCLSPRT16 WH	Pregalvanized	White	0.62"	1.63"	19.229"	0.281"
WBTCLSPRT18	Electrogalvaniz ed		0.62"	1.63"	21.198"	0.281"
WBTCLSPRT18 BA	Electrogalvaniz ed	Black	0.62"	1.63"	21.198"	0.281"
WBTCLSPRT18 WH	Electrogalvaniz ed	White	0.62"	1.63"	21.198"	0.281"
WBTCLSPRT20	Pregalvanized		0.62"	1.63"	23.167"	0.281"
WBTCLSPRT20 BA	Pregalvanized	Black	0.62"	1.63"	23.167"	0.281"
WBTCLSPRT20 WH	Pregalvanized	White	0.62"	1.63"	23.167"	0.281"
WBTCLSPRT24	Electrogalvaniz ed		0.62"	1.63"	27.104"	0.281"
WBTCLSPRT24 BA	Electrogalvaniz ed	Black	0.62"	1.63"	27.104"	0.281"
WBTCLSPRT24 WH	Electrogalvaniz ed	White	0.62"	1.63"	27.104"	0.281"
WBTCLSPRT6	Pregalvanized		0.62"	1.63"	9.386"	0.281"
WBTCLSPRT6B A	Pregalvanized	Black	0.62"	1.63"	9.386"	0.281"

CatalogNumber	Finish	Color	Height	Width	Length	Hole Size 1
WBTCLSPRT6W H	Pregalvanized	White	0.62"	1.63"	9.386"	0.281"
WBTCLSPRT8	Pregalvanized		0.62"	1.63"	11.354"	0.281"
WBTCLSPRT8B A	Pregalvanized	Black	0.62"	1.63"	11.354"	0.281"
WBTCLSPRT8W H	Pregalvanized	White	0.62"	1.63"	11.354"	0.281"

Table 2/2					
Catalog Number	Hole Size 2	Unit Weight			
WBTCLSPRT12	0.228"	1.1 lb			
WBTCLSPRT12BA	0.228"	1.1 lb			
WBTCLSPRT12WH	0.228"	1.1 lb			
WBTCLSPRT16	0.228"	1.5 lb			
WBTCLSPRT16BA	0.228"	1.5 lb			
WBTCLSPRT16WH	0.228"	1.5 lb			
WBTCLSPRT18	0.228"	1.6 lb			
WBTCLSPRT18BA	0.228"	1.6 lb			
WBTCLSPRT18WH	0.228"	1.6 lb			
WBTCLSPRT20	0.228"	1.9 lb			
WBTCLSPRT20BA	0.228"	1.9 lb			
WBTCLSPRT20WH	0.228"	1.9 lb			

Catalog Number	Hole Size 2	Unit Weight
WBTCLSPRT24	0.228"	1.9 lb
WBTCLSPRT24BA	0.228"	1.9 lb
WBTCLSPRT24WH	0.228"	1.9 lb
WBTCLSPRT6	0.228"	0.55 lb
WBTCLSPRT6BA	0.228"	0.55 lb
WBTCLSPRT6WH	0.228"	0.55 lb
WBTCLSPRT8	0.228"	0.8 lb
WBTCLSPRT8BA	0.228"	0.8 lb
WBTCLSPRT8WH	0.228"	0.8 lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

