

WBT Performance Cable Tray Ceiling Support



In the evolving landscape of cable management, the nVent CADDY WBT Performance Tray Ceiling Support is a simple and efficient alternative to traditional strut trapeze systems for wire basket tray installations. Engineered for simplicity and strength, this support solution not only anchors wire basket trays securely to the ceiling but also doubles as a splice point—making it a dual-function component that enhances both structural integrity and installation efficiency.

Compatible with varying nVent CADDY WBT Performance Cable Tray sizes, the ceiling support is precision-engineered to handle the weight of the trays with confidence. Its pre-punched design simplifies mounting with standard fasteners. Its compatibility with various finishes—including pre-galvanized, zinc electroplate, and powder coat options—adds aesthetic and functional versatility to any project.

FEATURES

Use as a center support or support provisioned from both ends

Designed to be used with the nVent CADDY WBT Performance Cable Tray Ground Splice and nVent CADDY WBT Performance Cable Tray Splice Kit

Supported with 3/8 or 1/2 in threaded rod

SPECIFICATIONS

Finish: Pregalvanized

Material: Steel

Table 1/2

Catalog Number	Color	Height	Width	Length	Hole Size 1	Hole Size 2
WBTCLSPRT12		0.62"	1.63"	15.292"	0.531"	0.228"
WBTCLSPRT12 BA	Black	0.62"	1.63"	15.292"	0.531"	0.228"

CatalogNumber	Color	Height	Width	Length	Hole Size 1	Hole Size 2
WBTCLSPRT12 WH	White	0.62"	1.63"	15.292"	0.531"	0.228"
WBTCLSPRT16		0.62"	1.63"	19.229"	0.531"	0.228"
WBTCLSPRT16 BA	Black	0.62"	1.63"	19.229"	0.531"	0.228"
WBTCLSPRT16 WH	White	0.62"	1.63"	19.229"	0.531"	0.228"
WBTCLSPRT18		0.62"	1.63"	21.198"	0.531"	0.228"
WBTCLSPRT18 BA	Black	0.62"	1.63"	21.198"	0.531"	0.228"
WBTCLSPRT18 WH	White	0.62"	1.63"	21.198"	0.531"	0.228"
WBTCLSPRT20		0.62"	1.63"	23.167"	0.531"	0.228"
WBTCLSPRT20 BA	Black	0.62"	1.63"	23.167"	0.531"	0.228"
WBTCLSPRT20 WH	White	0.62"	1.63"	23.167"	0.531"	0.228"
WBTCLSPRT24		0.62"	1.63"	27.104"	0.531"	0.228"
WBTCLSPRT24 BA	Black	0.62"	1.63"	27.104"	0.531"	0.228"
WBTCLSPRT24 WH	White	0.62"	1.63"	27.104"	0.531"	0.228"
WBTCLSPRT6		0.62"	1.63"	9.386"	0.531"	0.228"
WBTCLSPRT6B A	Black	0.62"	1.63"	9.386"	0.531"	0.228"

CatalogNumber	Color	Height	Width	Length	Hole Size 1	Hole Size 2
WBTCLSPRT6WH	White	0.62"	1.63"	9.386"	0.531"	0.228"
WBTCLSPRT8		0.62"	1.63"	11.354"	0.531"	0.228"
WBTCLSPRT8BA	Black	0.62"	1.63"	11.354"	0.531"	0.228"
WBTCLSPRT8WH	White	0.62"	1.63"	11.354"	0.531"	0.228"

Table 2/2

Catalog Number	Unit Weight
WBTCLSPRT12	1.1 lb
WBTCLSPRT12BA	1.1 lb
WBTCLSPRT12WH	1.1 lb
WBTCLSPRT16	1.5 lb
WBTCLSPRT16BA	1.5 lb
WBTCLSPRT16WH	1.5 lb
WBTCLSPRT18	1.6 lb
WBTCLSPRT18BA	1.6 lb
WBTCLSPRT18WH	1.6 lb
WBTCLSPRT20	1.9 lb
WBTCLSPRT20BA	1.9 lb
WBTCLSPRT20WH	1.9 lb

Catalog Number	Unit Weight
WBTCLSPRT24	1.9 lb
WBTCLSPRT24BA	1.9 lb
WBTCLSPRT24WH	1.9 lb
WBTCLSPRT6	0.55 lb
WBTCLSPRT6BA	0.55 lb
WBTCLSPRT6WH	0.55 lb
WBTCLSPRT8	0.8 lb
WBTCLSPRT8BA	0.8 lb
WBTCLSPRT8WH	0.8 lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

