

# WBT Performance Cable Tray Center Support



The nVent CADDY WBT Performance Tray Center Support is a simple and efficient way to support wire basket trays from a single threaded rod. The offset center tube helps ensure the tray is centered and secured, enhancing both structural integrity and improving project efficiency. Designed for light-duty cable support projects, installation is easy—simply hold the Center Support parallel to the tray, then turn perpendicular until you hear the Center Support lock into place.

Compatible with varying nVent CADDY WBT Performance Cable Tray sizes, the ceiling support is precision-engineered to handle the weight of the trays with confidence. Its pre-punched design simplifies mounting with standard fasteners. Its compatibility with various finishes—including pre-galvanized, zinc electroplate, and powder coat options—adds aesthetic and functional versatility to any project.

## FEATURES

Use as a central support when hanging with threaded rod

Designed to be used with the nVent CADDY WBT Performance Cable Tray Splice Kit

Supported with 3/8 or 1/2 in threaded rod

## SPECIFICATIONS

**Finish:** Pregalvanized

**Material:** Steel

Table 1/2

Catalog Number	Color	Width	Length	Height 1	Height 2	Hole Size 1
WBTCTSPRT12		2"	11.503"	0.62"	7"	0.281"
WBTCTSPRT12 WH	White	2"	11.503"	0.62"	7"	0.281"
WBTCTSPRT4		2"	4.14"	0.62"	7"	0.281"

CatalogNumber	Color	Width	Length	Height 1	Height 2	Hole Size 1
WBTCTSPRT4B A	Black	2"	4.14"	0.62"	7"	0.281"
WBTCTSPRT4 WH	White	2"	4.14"	0.62"	7"	0.281"
WBTCTSPRT6		2"	5.818"	0.62"	7"	0.281"
WBTCTSPRT6 WH	White	2"	5.818"	0.62"	7"	0.281"
WBTCTSPRT8		2"	7.502"	0.62"	7"	0.281"
WBTCTSPRT8 WH	White	2"	7.502"	0.62"	7"	0.281"

Table 2/2

Catalog Number	Hole Size 2	Unit Weight
WBTCTSPRT12	0.228"	0.556 lb
WBTCTSPRT12WH	0.228"	0.556 lb
WBTCTSPRT4	0.228"	0.318 lb
WBTCTSPRT4BA	0.228"	0.318 lb
WBTCTSPRT4WH	0.228"	0.318 lb
WBTCTSPRT6	0.228"	0.37 lb
WBTCTSPRT6WH	0.228"	0.37 lb
WBTCTSPRT8	0.228"	0.411 lb
WBTCTSPRT8WH	0.228"	0.411 lb

**WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

**Europe**

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

**Europe**

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

**APAC**

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**

