

WBT Performance Cable Tray Ground Bolt



The nVent CADDY WBT Performance Cable Tray Ground Bolt is a robust solution designed to ensure reliable grounding in cable tray installations where a separate ground wire is required. Engineered with a heavy-duty copper construction, this bolt allows the ground wire to run directly through it, enabling a secure connection to each tray section. This offering facilitates safety and compliance in environments where UL certification or grounding standards are mandatory.

Ideal for use in commercial and industrial settings, the Ground Bolt simplifies the grounding process while maintaining high performance and durability. Its straightforward installation and solid copper build make it a trusted choice for professionals seeking dependable grounding hardware

FEATURES

Easy-to-use, requiring only simple hand tools to install

Used to create a continuous grounded bond between sections of cable tray and can protect assets in case of a lightning strike

SPECIFICATIONS

Table 1/1					
Catalog Number	Material	Height	Length	Unit Weight	Width
WBTGRDBOLT	Copper Alloy	0.748"	1.402"	0.5 lb	0.748"

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE





©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.