

19" Drawer

Data Solutions



19" Drawers allow mounting of laptops, writing surfaces for easy operations. The SCHROFF 19" drawer has a load capacity of 15 KG, allowing a wide range of products to be assembled into the drawer.

CERTIFICATIONS



FEATURES

Static load-carrying capacity 15 kg

Optional writing surface

SPECIFICATIONS

Product Type: Cabinet/Rack Drawer

Material: Steel

Table 1/2

Catalog Number	Rack Height	Finish	Package Quantity	Color	Color Code	Front Finish
20110-054	1U	Powder Coated	1	Light Grey	RAL 7035	
20110-180	1U	Powder Coated	1	Black Grey	RAL 7021	

CatalogNumber	Rack Height	Finish	Package Quantity	Color	Color Code	Front Finish
20110-061	1U	Powder Coated	1			Anodized
20110-181	2U	Powder Coated	1	Black Grey	RAL 7021	
20110-063	3U	Powder Coated	1			Anodized
20110-062	2U	Powder Coated	1			Anodized
20110-182	3U	Powder Coated	1	Black Grey	RAL 7021	
20110-056	3U	Powder Coated	1	Light Grey	RAL 7035	
20110-055	2U	Powder Coated	1	Light Grey	RAL 7035	

Table 2/2

Catalog Number	Type	Works With
20110-054	Drawer	19" Cabinets
20110-180	Drawer	19" Cabinets
20110-061	Drawer	19" Cabinets
20110-181	Drawer	19" Cabinets
20110-063	Drawer	19" Cabinets
20110-062	Drawer	19" Cabinets
20110-182	Drawer	19" Cabinets
20110-056	Drawer	19" Cabinets
20110-055	Drawer	19" Cabinets

ADDITIONAL PRODUCT DETAILS

Please order 19" assembly kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE