

# Basic PDU, EB0xxx, 230 VAC, 1-PH

## Data Solutions

Modular, compact PDU. Ultra-Low Profile Design



### FEATURES

Enlogic Basic Power Distribution Units enable power in Cabinets as well as Open Frame Racks and Wall-Mount enclosures

Input Voltage 230 VAC, 1-phase

C13 and C19 outlets

1RU aluminum profile

Adjustable Toolless Mounting

### SPECIFICATIONS

Table 1/5

| Catalog Number | Product Family | Type      | Product Type | Socket Type       | Socket Quantity | Color |
|----------------|----------------|-----------|--------------|-------------------|-----------------|-------|
| EB0311         | Enlogic        | Basic PDU | Socket Strip | (12) C13          | 12              | Black |
| EB0322         | Enlogic        | Basic PDU | Socket Strip | (20) C13, (2) C19 | 22              | Black |
| EB0311-A       | Enlogic        | Basic PDU | Socket Strip | (12) C13          | 12              | Black |
| EB0317-A       | Enlogic        | Basic PDU | Socket Strip | (10) C13, (1) C19 | 11              | Black |
| EB0322-A       | Enlogic        | Basic PDU | Socket Strip | (30) C13, (6) C19 | 22              | Black |
| EB0303         | Enlogic        | Basic PDU | Socket Strip | (6) C19           | 6               | Black |
| EB0321         | Enlogic        | Basic PDU | Socket Strip | (20) C13          | 20              | Black |

| CatalogNumber | Product Family | Type      | Product Type | Socket Type       | SocketQuantity | Color |
|---------------|----------------|-----------|--------------|-------------------|----------------|-------|
| EB0328        | Enlogic        | Basic PDU | Socket Strip | (24) C13, (6) C19 | 30             | Black |
| EB0337        | Enlogic        | Basic PDU | Socket Strip | (36) C13, (6) C19 | 42             | Black |
| EB0332        | Enlogic        | Basic PDU | Socket Strip | (30) C13, (6) C19 | 36             | Black |
| EB0318-A      | Enlogic        | Basic PDU | Socket Strip | (12) C13, (1) C19 | 13             | Black |
| EB0313        | Enlogic        | Basic PDU | Socket Strip | (12) C13          | 12             | Black |
| EB0305        | Enlogic        | Basic PDU | Socket Strip | (6) C19           | 6              | Black |

Table 2/5

| Catalog Number | Circuit Breaker      | Switched Outlets | Circuit Breaker Quantity | Power Rating                               | Input Cable Location | Input Voltage |
|----------------|----------------------|------------------|--------------------------|--------------------------------------------|----------------------|---------------|
| EB0311         | No Circuit Breaker   | No               | 0                        | 3.7 kVA                                    | Front Feed           | 200 – 240V    |
| EB0322         | No Circuit Breaker   | No               | 0                        | 3.7 kVA                                    | Top Feed             | 100 – 240V    |
| EB0311-A       | 16 A, 1-pole, Hy-Mag | No               | 0                        |                                            | Front Feed           | 100 – 240V    |
| EB0317-A       | 16 A, 1-pole, Hy-Mag | No               | 0                        |                                            | Front Feed           | 100 – 240V    |
| EB0322-A       | 16 A, 1-pole, Hy-Mag | No               | 0                        |                                            | Front Feed           | 100 – 240V    |
| EB0303         | 16 A, 1-pole, Hy-Mag | No               | 2                        | 7.4 kVA                                    | Front Feed           | 200 – 240V    |
| EB0321         | 16 A, 1-pole, Hy-Mag | No               | 2                        | 7.4 kVA                                    | Top Feed             | 200 – 240V    |
| EB0328         | 16 A, 1-pole, Hy-Mag | No               | 2                        | 7.4 kVA                                    | Top Feed             | 200 – 240V    |
| EB0337         | 16 A, 1-pole, Hy-Mag | No               | 2                        | 5 kVA North America, 7.4 kVA International | Top Feed             | 200 – 240V    |
| EB0332         | 16 A, 1-pole, Hy-Mag | No               | 3                        |                                            | Top Feed             | 200 – 240V    |

| CatalogNumber | Circuit Breaker      | Switched Outlets | Circuit Breaker Quantity | Power Rating | Input Cable Location | Input Voltage |
|---------------|----------------------|------------------|--------------------------|--------------|----------------------|---------------|
| EB0318-A      | 16 A, 1-pole, Hy-Mag | No               | 2                        |              | Front Feed           | 100 – 240V    |
| EB0313        | 16 A, 1-pole, Hy-Mag | No               | 2                        | 7.4 kVA      | Front Feed           | 200 – 240V    |
| EB0305        | 16 A, 1-pole, Hy-Mag | No               | 6                        |              | Front Feed           | 200 – 240V    |

Table 3/5

| Catalog Number | Phase | Interrupt Rating | Max Power Input | Nominal Voltage | On/Off Switch Included | Output Voltage |
|----------------|-------|------------------|-----------------|-----------------|------------------------|----------------|
| EB0311         | 1 PH  | 5kAIC            | 3.68 kVA        | 230V            | No                     | 230VAC         |
| EB0322         | 1 PH  | 5kAIC            | 3.68 kVA        | 230V            | No                     | 230VAC         |
| EB0311-A       | 1 PH  | 5kAIC            | 3.68 kVA        |                 |                        | 100 – 240VAC   |
| EB0317-A       | 1 PH  | 5kAIC            | 3.68 kVA        |                 |                        | 100 – 240VAC   |
| EB0322-A       | 1 PH  | 5kAIC            | 3.68 kVA        |                 |                        | 100 – 240VAC   |
| EB0303         | 1 PH  | 5kAIC            | 7.44 kVA        | 230V            | No                     | 230VAC         |
| EB0321         | 1 PH  | 5kAIC            | 7.44 kVA        | 230V            | No                     | 230VAC         |
| EB0328         | 1 PH  | 5kAIC            | 7.44 kVA        | 230V            | No                     | 230VAC         |
| EB0337         | 1 PH  | 5kAIC            | 7.44 kVA        | 230V            | No                     | 230VAC         |
| EB0332         | 1 PH  | 5kAIC            | 11.0 kVA        |                 |                        | 200 – 240VAC   |
| EB0318-A       | 1 PH  | 5kAIC            | 3.68 kVA        |                 |                        | 100 – 240VAC   |
| EB0313         | 1 PH  | 5kAIC            | 7.44 kVA        | 230V            | No                     | 230VAC         |
| EB0305         | 1 PH  | 5kAIC            | 14.4 kVA        |                 |                        | 200 – 240VAC   |

Table 4/5

| Catalog Number | Amperage (Derated Amperage)                            | Plug Type              | Rack Units | Removable Input Cable | Metering Type | Material |
|----------------|--------------------------------------------------------|------------------------|------------|-----------------------|---------------|----------|
| EB0311         | 16 A                                                   | IEC 60309 316P6 (IP44) | 1U         | Yes                   | None          | Steel    |
| EB0322         | 16 A                                                   | IEC 60309 316P6 (IP44) | 0U         | Yes                   | None          | Steel    |
| EB0311-A       | 16 A                                                   | C20                    | 1U         | Yes                   | None          |          |
| EB0317-A       | 20 A (16 A)<br>North America,<br>16 A<br>International | C20                    | 0U         | Yes                   | None          |          |
| EB0322-A       | 20 A (16 A)<br>North America,<br>16 A<br>International | C20                    | 0U         | Yes                   | None          |          |
| EB0303         | 32 A                                                   | IEC 60309 332P6 (IP44) | 0U         | No                    | None          | Steel    |
| EB0321         | 32 A                                                   | IEC 60309 332P6 (IP44) | 0U         | No                    | None          | Steel    |
| EB0328         | 32 A                                                   | IEC 60309 332P6 (IP44) | 0U         | No                    | None          | Steel    |
| EB0337         | 30 A (24 A)<br>North America,<br>32 A<br>International | IEC 60309 332P6 (IP44) | 0U         | No                    | None          | Steel    |
| EB0332         | 63 A                                                   | IEC 60309 363P6 (IP44) | 0U         | No                    | None          |          |
| EB0318-A       | 16 A                                                   | C20                    | 2U         | Yes                   | None          |          |
| EB0313         | 32 A                                                   | IEC 60309 332P6 (IP44) | 1U         | No                    | None          | Steel    |
| EB0305         | 63 A                                                   | IEC 60309 363P6 (IP44) | 1U         | No                    | None          |          |

Table 5/5

| Catalog Number | Finish        | Height | Width   | Depth  | Weight | Package Quantity |
|----------------|---------------|--------|---------|--------|--------|------------------|
| EB0311         | Powder Coated | 1.69in | 17.48in | 1.61in | 4.96lb | 1                |

| CatalogNumber | Finish        | Height  | Width   | Depth  | Weight  | Package Quantity |
|---------------|---------------|---------|---------|--------|---------|------------------|
| EB0322        | Powder Coated | 32.17in | 2.05in  | 2.09in | 7.94lb  | 1                |
| EB0311-A      |               |         |         |        |         | 1                |
| EB0317-A      |               |         |         |        |         | 1                |
| EB0322-A      |               |         |         |        |         | 1                |
| EB0303        | Powder Coated | 1.69in  | 17.48in | 7.76in |         | 1                |
| EB0321        | Powder Coated | 32.17in | 2.05in  | 2.09in | 12.35lb | 1                |
| EB0328        | Powder Coated | 58.66in | 2.05in  | 2.09in | 20.9lb  | 1                |
| EB0337        | Powder Coated | 58.66in | 2.05in  | 2.09in | 15.87lb | 1                |
| EB0332        |               |         |         |        |         | 1                |
| EB0318-A      |               |         |         |        |         | 1                |
| EB0313        | Powder Coated | 1.69in  | 17.48in | 7.76in | 11.46lb | 1                |
| EB0305        |               |         |         |        |         | 1                |

## ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**