

Basic PDU, EB0xxx, 400 VAC, 3-PH

Data Solutions

Modular, compact PDU. Ultra-Low Profile Design



FEATURES

Enlogic Basic Power Distribution Units enable power in Cabinets as well as Open Frame Racks and Wall-Mount enclosures

Input Voltage 400 VAC, 3-phase

C13 and C19 outlets

1RU aluminum profile

Adjustable Toolless Mounting

SPECIFICATIONS

Table 1/5

Catalog Number	Product Family	Type	Product Type	Socket Type	Socket Quantity	Color
EB0403	Enlogic	Basic PDU	Socket Strip	(36) C13, (6) C19	42	Black
EB0450	Enlogic	Basic PDU	Socket Strip	(21) C13/C19	42	Black
EB0811	Enlogic	Basic PDU	Socket Strip	(30) C13, (12) C19	42	Black
EB0850	Enlogic	Basic PDU	Socket Strip	(24) C13/C15, (24) C13/C15/C19/C21	48	Black

Table 2/5

Catalog Number	Circuit Breaker	Switched Outlets	Circuit Breaker Quantity	Power Rating	Input Cable Location	Input Voltage
EB0403	No Circuit Breaker	No	0	11.0 kVA	Top Feed	380 – 415V

CatalogNumber	Circuit Breaker	Switched Outlets	Circuit Breaker Quantity	Power Rating	Input Cable Location	Input Voltage
EB0450	No Circuit Breaker	No	0	11.5 kVA North America, 11.0 kVA International	Top Feed	380 – 415V
EB0811	16 A, 1-pole, Hy-Mag	No	6	22.0 kVA	Top Feed	380 – 415V
EB0850	16 A, 1-pole, Hy-Mag	No	6	17.3 kVA North America, 22.1 kVA International	Top Feed	380 – 415V

Table 3/5

Catalog Number	Phase	Nominal Voltage	Max Power Input	On/Off Switch Included	Amperage (Derated Amperage)	Output Voltage
EB0403	3 PH	415V	11.0 kVA	No	16 A	230VAC
EB0450	3 PH	415V	11.5 / 11.0 kVA	No	20 A (16 A) North America, 16 A International	208 – 230VAC
EB0811	3 PH	415V	22.0 kVA	No	32 A	230VAC
EB0850	3 PH	415V	17.3 / 22.1 kVA	No	30 A (24 A) North America, 32 A International	208 – 230VAC

Table 4/5

Catalog Number	Rack Units	Plug Type	Metering Type	Removable Input Cable	Material	Finish
EB0403	0U	IEC 60309 516P6 (IP44)	None	No	Steel	Powder Coated
EB0450	0U	IEC 60309 520P6/516P6	None	No	Steel	Powder Coated
EB0811	0U	IEC 60309 532P6 (IP44)	None	No	Steel	Powder Coated
EB0850	0U	IEC 60309 530P6/532P6	None	No	Steel	Powder Coated

Table 5/5

Catalog Number	Height	Width	Depth	Weight	Package Quantity
----------------	--------	-------	-------	--------	------------------

EB0403	58.66in	2.05in	2.09in	13.45lb	1
EB0450	58.66in	2.2in	2.17in	20.9lb	1
EB0811	68.9in	2.17in	2.09in	19.84lb	1
EB0850	70.8in	2.2in	2.17in	22lb	1

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE