

Bonding and Grounding Horizontal Ground Bar Kits

Data Solutions



The Horizontal Ground Bar Kits mount horizontally on a rack, providing a convenient place to connect equipment grounds. The kits include a ground bar with mounting hardware; eight #6-32 x 14 machine screws, and eight #6 ring terminals.

These components meet open frame rack and cabinet bonding and grounding requirements for telecommunication room and data center applications.

FEATURES

Components specially designed to efficiently facilitate reliable connections

Enable system to meet equipment manufacturer grounding requirements

Components fit EIA 310-D-rated open frame racks

Made of electrolytic tough-pitch 110 copper alloy

SPECIFICATIONS

Table 1/1

Catalog Number	Article Number	Height	Width	Material	Finish	Thickness
DG19	17266	1in	19.25in	Copper	Electroplated, Tinned	0.25in
DG23	17267	1in	23.25in	Copper	Electroplated, Tinned	0.25in

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE