

Branch Line Restraint Structure Attachment to Steel

Data Solutions



CERTIFICATIONS







FEATURES

Swivel barrel nut accepts 3/8" or 1/2" (M10 or M12) threaded rod

Attaches to steel members with self-drilling/tapping screw

SPECIFICATIONS

Table 1/2								
Catalog Number	Material	Finish	Rod Size (RS)	Flange Thickness (FT)	Height (H)	Length (L)		
CSBBRS1EG	Steel	Electrogalvaniz ed	0.375in, 0.5in	0.1 - 0.5in	1.11in	1.59in		


Table 2/2						
Catalog Number	Width (W)	Screw Diameter (Sc)	Screw Length (L)			

CSBBRS1EG	1.06in	12in	1.25in
	1.06in	12in	1.25in

ADDITIONAL PRODUCT DETAILS

Branch line structural attachments are for restraint only and not for the hanging of fire sprinkler piping.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE