

Clevis Bolt Spacer

Data Solutions



FEATURES

Seismically braces the 401 Clevis Hanger series for lateral load

Retrofit ability allows the spacer to be installed after the clevis and pipe are installed

Ears easily pinch closed around the clevis hanger cross bolt with pliers

FM® Specification Tested (up to 8" Pipe Size)

SPECIFICATIONS

Finish: Electrogalvanized


Material: Steel

Table 1/1

Catalog Number	Pipe Size	Width (W)	Height (H)	Thickness (T)	Depth (D)
CSBCS0100	1in	1.21in	0.51in	0.07in	0.51in
CSBCS0125	1.25in min	1.55in	0.51in	0.07in	0.51in
CSBCS0150	1.5in	1.71in	0.51in	0.07in	0.51in
CSBCS0200	2in min	2.28in	0.51in	0.07in	0.51in

Catalog Number	Pipe Size	Width (W)	Height (H)	Thickness (T)	Depth (D)
CSBCS0250	2.5in	2.78in	0.67in	0.07in	0.65in
CSBCS0300	3in	3.41in	0.67in	0.07in	0.65in
CSBCS0350	3.5in	3.91in	0.67in	0.07in	0.65in
CSBCS0400	4in	4.41in	0.67in	0.07in	0.65in
CSBCS0500	5in	5.5in	0.98in	0.07in	0.9in
CSBCS0600	6in	6.56in	0.98in	0.07in	0.9in
CSBCS0800	8in	8.56in	1.22in	0.07in	1.09in
CSBCS1000	10in	10.52in	1.22in	0.07in	1.09in
CSBCS1200	12in	12.52in	1.22in	0.07in	1.09in

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE