

Concept Panels

Data Solutions



Concept panels are taller and wider than corresponding NEMA-size panels.

FEATURES

Painted white or conductive finish

Include a formed flange along any side that is longer than 22.20 in (564 mm)

Optional wood panels are made of 3/4-in plywood, pre-cut and pre-drilled to install on panel mounting studs in the rear of the cabinet

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Height	Width	Material	Finish	Color
CP3220W	23786	30.2in	18.2in	Plywood	Smooth Matte	
CP4420W	23787	42.2in	18.2in	Plywood	Smooth Matte	
CP2020W	23785	18.2in	18.2in	Plywood	Smooth Matte	
CP4420	23783	42.2in	18.2in	Mild Steel	Powder Coated	White
CP3220	23782	30.2in	18.2in	Mild Steel	Powder Coated	White

CatalogNumber	Article Number	Height	Width	Material	Finish	Color
CP5620	23784	53.2in	18.2in	Mild Steel	Powder Coated	White

Table 2/2

Catalog Number	Article Number	Thickness	Type	Gauge
CP3220W	23786	0.75in	Wood	
CP4420W	23787	0.75in	Wood	
CP2020W	23785	0.75in	Wood	
CP4420	23783	12in	Painted Steel	12ga
CP3220	23782	12in	Painted Steel	12ga
CP5620	23784	12in	Painted Steel	12ga

ADDITIONAL PRODUCT DETAILS

Catalog number CP4230 is used on Concept disconnect enclosures.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE