

# Crimping Compression Tool, Battery Powered

## Data Solutions



### FEATURES

Wide cross section range

Ergonomic design

High-performance 18 volt lithium-ion battery for increased work capacity

Automatic retraction stop (ARS) after completed crimping

Lightweight and easy to use

Includes easy-to-carry custom case

### SPECIFICATIONS

Table 1/1

| Catalog Number | Applied Force | System                    | Dies                     | Crimping Shape | Conductor Size   |
|----------------|---------------|---------------------------|--------------------------|----------------|--|
| MLB            | 11240lb       | Battery-powered hydraulic | RKML series, PKML series | Hexagon        | #10 Stranded - 500 kcmil Stranded, 6 mm <sup>2</sup> Stranded - 240 mm <sup>2</sup> Stranded |
| M3B            | 26980lb       | Battery-powered hydraulic | RKM3 series, PKM3 series | Hexagon        | #6 Stranded - 800 kcmil Stranded, 16 mm <sup>2</sup> Stranded - 400 mm <sup>2</sup> Stranded |

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**