

Special Track Work Mold Only, Power, 2/0 Concentric, Left Hand

Data Solutions

CATALOG NUMBER

PBJT503LHM



FEATURES

Replacement molds designed for bonding structures in power bond applications

To be used with factory-formed terminals

Available in either left or right-hand orientation

PRODUCT ATTRIBUTES

Material: Graphite

Bond Terminal Style: J

Rail Type: Crane Rail Profiles

Conductor Size: 2/0 Concentric

Conductor Outer Diameter, Nominal: 0.42in

Welder Style: T5

Orientation: Left Hand

Mold Only: Yes

Welding Material: PB45 or PB45PLUSF80, Sold Separately

Handle Clamp: B323BX, Sold Separately

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE