

Cable to Web of Rail Mold Only, Signal, Field-made Bond Terminal Style, 50 mm² Solid, Right Hand

Data Solutions

CATALOG NUMBER

SBWW6RH



FEATURES

Replacement mold designed for the installation of track circuits and jumper bonds to the neutral axis

PRODUCT ATTRIBUTES

Material: Graphite

Rail Type: 85 lb to 141 lb T-Rail Sections

Bond Terminal Style: Field-made

Conductor Size: 50 mm² Solid

Conductor Outer Diameter, Nominal: 0.32in

Welder Style: T21

Orientation: Right Hand

Mold Only: Yes

Welding Material: SB32 or SB25PLUSF80, Sold Separately

Handle Clamp: C105B, Sold Separately

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE