

Varistar CP Glazed Door, With 1-Point Locking, Key Plate Only, RAL 7021, 47 U, 2200H 800W

Data Solutions

CATALOG NUMBER

21630-492



Varistar CP Glass Door Single Point Locking for IP 20 applications.

FEATURES

St, 1.5 mm

Security glass, 6 mm

Key lock cover

Opening angle 180°

PRODUCT ATTRIBUTES

Rack Height: 47U

Locking Type: Single Point Locking

Package Quantity: 1

Color: Black Grey

Color Code: RAL 7021

Complies With: IEC 61587-1

Finish: Powder Coated

Material: Steel; Glass

Product Family: Varistar CP

Product Type: Cabinet Door

Protection Rating: IP20

Type: Glass Door

Works With: Varistar CP

Net Weight: 46.752kg

ADDITIONAL PRODUCT DETAILS

24U - 33U IP20 doors have 2 hinges, 38U - 52U IP20 doors have 3 hinges to ensure robust IP20 closing structures for taller cabinets

Please order lever handle 24630003 and the DIN lock separately if you want to replace the 1333 DIN lock lever handle

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE