

Basic PDU, EB0311, 230 VAC, 1-PH, 16 A

Data Solutions

CATALOG NUMBER

EB0311



Modular, compact PDU. Ultra-Low Profile Design

FEATURES

Enlogic Basic Power Distribution Units enable power in Cabinets as well as Open Frame Racks and Wall-Mount enclosures

Input Voltage 230 VAC, 1-phase

C13 and C19 outlets

1RU aluminum profile

Adjustable Toolless Mounting

PRODUCT ATTRIBUTES

Product Family: Enlogic

Type: Basic PDU

Product Type: Socket Strip

Socket Type: (12) C13

Socket Quantity: 12

Color: Black

Circuit Breaker: No Circuit Breaker

Switched Outlets: No

Circuit Breaker Quantity: 0

Power Rating: 3.7 kVA

Input Cable Location: Front Feed

Input Voltage: 200 – 240V

Phase: 1 PH

Interrupt Rating: 5kAIC

Max Power Input: 3.68 kVA

Nominal Voltage: 230V

On/Off Switch Included: No

Output Voltage: 230VAC

Amperage (Derated Amperage): 16 A

Plug Type: IEC 60309 316P6 (IP44)

Rack Units: 1U

Removable Input Cable: Yes

Metering Type: None

Material: Steel

Finish: Powder Coated

Height: 1.69in

Width: 17.48in

Depth: 1.61in

Weight: 4.96lb

Package Quantity: 1

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE