

CableTek-EC Vertical Cable Manager Double Finger, 84.00x6.50x20.85, Black, Steel

Data Solutions

CATALOG NUMBER

EC6DF7



The CableTek-EC Cable manager is attached to the sides and/or in between open-frame racks to economically provide support, easy access and proper cable management with easy cable installation for Network rack-mount equipment. The front side provides support, management and high cable capacity for patch cords with easy-to-remove front covers standard. The rear of the manager provides the same support for horizontal cabling (Cat 5e, 6, 6A and fiber). CableTek-EC Vertical Cable Managers are available in single- and double-sided versions.

FEATURES

Universal mounting pattern for 2- and 4-post open-frame racks

Easy-to-install with self-aligning, self-captivating carriage bolts for single-sided attachment

Arrowhead supporting fingers provide easy insertion, removal and alignment of Cat 5e, 6, 6A and other cable types

Deep cable depth provides smooth transition of cables from vertical to horizontal positions

Large feed-through holes and pre-scored grommets provide cable feed from front to back of cable manager

Unobstructed cable access for all rack unit locations

Extra deep cable channel for maximum cable density has multiple cable tie-down points

Standard front cover, with field installed snap hinges, provides cable access from right, left or neutral

Double-sided models with supporting fingers include front central latching cover and rear snap-on cover

Double-sided models with posts and gates support and contain cables. Five posts and gates are included; additional sets are available as accessories

Posts snap into pre-punched holes in the back of the cable manager

Gates snap onto posts, open from left or right as needed and swing 280° for cable access. Posts can be used alone as slack spools to control long patch cords

The single-sided cable manager can be upgraded with CableTek Post and Gates Kits

CableTek Rear Cover is sold separately as an accessory for vertical cable managers with posts and gates, and is fully field installable; no tools needed

Easy-to-remove front cover is multi-formed, light-weight aluminum with high-strength, black composite snap-on hinge points and hinges right, left or neutral

Rear posts and gates on double-sided models are high-strength, black composite with all edges rounded

Arrowhead supporting fingers are high-strength, black composite with all edges rounded

PRODUCT ATTRIBUTES

Article Number: 26283

Width: 6in

Material: Mild Steel

Finish: Powder Coated

Color: Jet Black

Color Code: RAL 9005

Thickness: 14ga

Height: 7ft

Rack Units: 45U

Weight: 70lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE