


MI PDU, 2U, 100A(80A)NA/96A Int, 380-415V, 3P Wye, 18 CB, (18)4-in-1

Data Solutions

CATALOG NUMBER

EN1965



The Advantage Series Input Metered PDU family offers energy metering with advanced power and environmental monitoring options. Comprehensive monitoring at both the input phase and circuit breaker levels offers advanced alerts of potential overloads. Billing-grade metering provides accurate power consumption data for energy use optimization. The hot-swappable network management controller features Gigabit and redundant ethernet communication with advanced support for external environmental sensors and rack security access solutions.

PRODUCT ATTRIBUTES

Product Family: Enlogic

Product Type: Socket Strip

Socket Type: (18) C13/C15/C19/C21

Color: Black

Switched Outlets: No

Circuit Breaker: 20 A

Power Rating: 57.6 kVA North America; 66.2 kVA International

Circuit Breaker Quantity: 18

Input Voltage: 380 – 415V

Phase: 3 PH

Number of Poles: 1

Output Voltage: 208 – 230VAC

Nominal Voltage: 415V

Plug Type: IEC 60309 5125P6W (IP67)

Removable Input Cable: No

Amperage (Derated Amperage): 100 A (80 A) North America; 96 A International

Finish: Powder Coated

Rack Units: 2U

Material: Steel

Type: Intelligent PDU

Height: 3.43in

Width: 17.48in

Depth: 10.59in

Weight: 28.66lb

Package Quantity: 1

ADDITIONAL PRODUCT DETAILS

43 mm L x 444 mm W x 269 mm D, (269 mm D at CB)

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE