

# ProLine V/D Server Cabinet Fan/Filter Type 1, 2000x600x1000mm, Black, Steel

## Data Solutions

### CATALOG NUMBER

**PSC20610BFP**



ProLine Voice/Data Server Cabinets are ideal for factory floors, warehouses and other remote locations that require filtration of ambient air to protect network equipment.

### INDUSTRY STANDARDS

UL508A Listed; Type 1; File No. E61997

cUL Listed per CSA C22.2 No 94; Type 1; File No. E61997

EIA RS-310-D

### FEATURES

Gasketed covers and air intake filters keep contaminants away

Removable filters can be cleaned to maintain optimal performance

Fan and filter package provides up to 600 CFM of filtered air to cool equipment

Three-point locking handles on all doors provide easy but controlled access; two keys included

Rack angles are infinitely adjustable from front to rear for positioning flexibility

Mobile base provides easy placement of cabinet

Mobile base includes casters, levelers and gland plate

Levelers and anti-tip bracket secure cabinet to the floor

### PRODUCT ATTRIBUTES

Article Number: 15337

Height (H): 86.74in

Width (W): 23.94in

Depth (D): 39.34in

Material: Mild Steel

Finish: Powder Coated

Color: Jet Black

Color Code: RAL 9005

Thickness (T): 16ga


Hole Type: Square

Rack Units: 42U

Cabinet Type: Server

Weight: 414lb

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**