

Intelligent PDU, EN1xxx, 230 VAC, 1-PH

Data Solutions

Modular, compact intelligent PDU with inlet metering. Ultra-Low Profile Design



FEATURES

Enlogic EN1xxx Intelligent Power Distribution Units monitors input power of the entire PDU, provides billing grade unit level monitoring

High Visibility Data Display and Interactive Graphic Display

Measure circuit breaker loads across redundant feeds to avoid accidental downtime

Enables smart load balancing for power efficiency and maximized capacity utilization

Gigabit Ethernet Interface and redundant Ethernet (10/100)

iPDU DC power redundancy solution for up to 64 PDU's

Toolless Hot-Swap Controller

Input voltage 230 VAC, 1-phase

C13, C19 outlets

SPECIFICATIONS

Table 1/5

Catalog Number	Product Family	Type	Product Type	Socket Type	Socket Quantity	Color
EN1326	Enlogic	Intelligent PDU	Socket Strip	(20) C13, (4) C19	24	Black
EN1325	Enlogic	Intelligent PDU	Socket Strip	(20) C13, (4) C19	24	Black
EN1337	Enlogic	Intelligent PDU	Socket Strip	(36) C13, (6) C19	42	Black
EN1350	Enlogic	Intelligent PDU	Socket Strip	(20) C13/C15, (20) C13/C15/C19/C21	40	Black

CatalogNumber	Product Family	Type	Product Type	Socket Type	SocketQuantity	Color
EN1380	Enlogic	Intelligent PDU	Socket Strip	(16) Locking C13/C15, (16) Locking C13/C15/C19/C21	32	Black

Table 2/5

Catalog Number	Circuit Breaker	Switched Outlets	Circuit Breaker Quantity	Power Rating	Input Cable Location	Input Voltage
EN1326	No Circuit Breaker	No	0	3.7 kVA	Top Feed	100 – 240V
EN1325	16 A, 1-pole, Hy-Mag	No	2	7.4 kVA	Top Feed	200 – 240V
EN1337	16 A, 1-pole, Hy-Mag	No	2	7.4 kVA	Top Feed	200 – 240V
EN1350	20 A, 1-pole, Hy-Mag	No	2	7.4 kVA	Top Feed	200 – 240V
EN1380	20 A, 1-pole, Hy-Mag	No	2	7.4 kVA	Top Feed	200 – 240V

Table 3/5

Catalog Number	Phase	Interrupt Rating	Nominal Voltage	Max Power Input	On/Off Switch Included	Amperage (Derated Amperage)
EN1326	1 PH	5kAIC	230V	3.3 kVA	No	16 A
EN1325	1 PH	5kAIC	230V	7.44 kVA	No	32 A
EN1337	1 PH	5kAIC	230V	7.44 kVA	No	32 A
EN1350	1 PH	5kAIC	230V	7.44 kVA	No	32 A
EN1380	1 PH	5kAIC	230V	7.44 kVA	No	32 A

Table 4/5

Catalog Number	Output Voltage	Rack Units	Plug Type	Metering Type	Removable Input Cable	Material
EN1326	230VAC	0U	IEC 60309 316P6 (IP44)	Input	Yes	Steel

CatalogNumber	Output Voltage	Rack Units	Plug Type	Metering Type	Removable Input Cable	Material
EN1325	230VAC	0U	IEC 60309 332P6 (IP44)	Input	No	Steel
EN1337	230VAC	0U	IEC 60309 332P6 (IP44)	Input	No	Steel
EN1350	230VAC	0U	IEC 60309 332P6 (IP44)	Input	No	Steel
EN1380	230VAC	0U	IEC 60309 332P6 (IP44)	Input	No	Steel

Table 5/5

Catalog Number	Finish	Height	Width	Depth	Weight	Package Quantity
EN1326	Powder Coated	58.66in	2.05in	2.09in	15.43lb	1
EN1325	Powder Coated	58.66in	2.05in	2.09in	15.62lb	1
EN1337	Powder Coated	68.9in	2.05in	2.09in	17.86lb	1
EN1350	Powder Coated	58.66in	2.2in	2.17in	18.08lb	1
EN1380	Powder Coated	58.66in	2.2in	2.17in	17.64lb	1

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE