

Intelligent PDU, EN2xxx, 230 VAC, 1-PH

Data Solutions

Modular, compact intelligent PDU with inlet metering. Ultra-Low Profile Design



FEATURES

Enlogic EN2xxx Intelligent Power Distribution Units monitors input power of the entire PDU and offers remote switching of individual outlets, provides billing grade unit level monitoring

High Visibility Data Display and Interactive Graphic Display

Measure circuit breaker loads across redundant feeds to avoid accidental downtime

Enables smart load balancing for power efficiency and maximized capacity utilization

Gigabit Ethernet Interface and redundant Ethernet (10/100)

iPDU DC power redundancy solution for up to 64 PDU's

Toolless Hot-Swap Controller

Input voltage 230 VAC, 1-phase

C13, C19 outlets

SPECIFICATIONS

Table 1/5

Catalog Number	Product Family	Type	Product Type	Socket Type	Socket Quantity	Color
EN2326	Enlogic	Intelligent PDU	Socket Strip	(20) C13, (4) C19	24	Black
EN2325	Enlogic	Intelligent PDU	Socket Strip	(20) C13, (4) C19	24	Black
EN2329	Enlogic	Intelligent PDU	Socket Strip	(24) C13, (8) C19	32	Black
EN2350	Enlogic	Intelligent PDU	Socket Strip	(20) C13/C15, (20) C13/C15/C19/C21	40	Black

CatalogNumber	Product Family	Type	Product Type	Socket Type	SocketQuantity	Color
EN2380	Enlogic	Intelligent PDU	Socket Strip	(16) Locking C13/C15, (16) Locking C13/C15/C19/C21	32	Black

Table 2/5

Catalog Number	Circuit Breaker	Switched Outlets	Circuit Breaker Quantity	Power Rating	Input Cable Location	Input Voltage
EN2326	No Circuit Breaker	Yes	0	3.7 kVA	Top Feed	100 – 240V
EN2325	16 A, 1-pole, Hy-Mag	Yes	2	7.4 kVA	Top Feed	200 – 240V
EN2329	16 A, 1-pole, Hy-Mag	Yes	2	7.4 kVA	Top Feed	200 – 240V
EN2350	20 A, 1-pole, Hy-Mag	Yes	2	7.4 kVA	Top Feed	200 – 240V
EN2380	20 A, 1-pole, Hy-Mag	Yes	2	7.4 kVA	Top Feed	200 – 240V

Table 3/5

Catalog Number	Phase	Max Power Input	Nominal Voltage	On/Off Switch Included	Output Voltage	Amperage (Derated Amperage)
EN2326	1 PH	3.68 kVA	230V	Yes	230VAC	16 A
EN2325	1 PH	7.44 kVA	230V	Yes	230VAC	32 A
EN2329	1 PH	7.44 kVA	230V	Yes	230VAC	32 A
EN2350	1 PH	7.44 kVA	230V	Yes	230VAC	32 A
EN2380	1 PH	7.44 kVA	230V	Yes	230VAC	32 A

Table 4/5

Catalog Number	Plug Type	Rack Units	Removable Input Cable	Metering Type	Material	Finish
EN2326	IEC 60309 316P6 (IP44)	0U	Yes	Input	Steel	Powder Coated

CatalogNumber	Plug Type	Rack Units	Removable Input Cable	Metering Type	Material	Finish
EN2325	IEC 60309 332P6 (IP44)	0U	No	Input	Steel	Powder Coated
EN2329	IEC 60309 332P6 (IP44)	0U	No	Input	Steel	Powder Coated
EN2350	IEC 60309 332P6 (IP44)	0U	No	Input	Steel	Powder Coated
EN2380	IEC 60309 332P6 (IP44)	0U	No	Input	Steel	Powder Coated

Table 5/5

Catalog Number	Height	Width	Depth	Weight	Package Quantity	Interrupt Rating
EN2326	58.66in	2.05in	2.09in	15.87lb	1	5kAIC
EN2325	68.9in	2.05in	2.09in	20.9lb	1	5kAIC
EN2329	68.9in	2.05in	2.09in	18.74lb	1	5kAIC
EN2350	58.66in	2.2in	2.95in	20.06lb	1	5kAIC
EN2380	58.66in	2.2in	2.95in		1	5kAIC

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE