

# Intelligent PDU, EN2xxx, 230 VAC, 1-PH

# **Data Solutions**

Modular, compact intelligent PDU with inlet metering. Ultra-Low Profile Design

#### **FEATURES**

Enlogic EN2xxx Intelligent Power Distribution Units monitors input power of the entire PDU and offers remote switching of individual outlets, provides billing grade unit level monitoring

High Visibility Data Display and Interactive Graphic Display

Measure circuit breaker loads across redundant feeds to avoid accidental downtime

Enables smart load balancing for power efficiency and maximized capacity utilization

Gigabit Ethernet Interface and redundant Ethernet (10/100)

iPDU DC power redundancy solution for up to 64 PDU's

Toolless Hot-Swap Controller

Input voltage 230 VAC, 1-phase

C13, C19 outlets

#### **SPECIFICATIONS**

	Table 1/5							
Catalog Number	Product Family	Туре	Product Type	Socket Type	Socket Quantity	Color		
EN2326	Enlogic	Intelligent PDU	Socket Strip	(20) C13, (4) C19	24	Black		
EN2316-A	Enlogic	Intelligent PDU	Socket Strip	(12) C13, (4) C19	16	Black		
EN2317	Enlogic	Intelligent PDU	Socket Strip	(12) C13, (4) C19	16	Black		
EN2325	Enlogic	Intelligent PDU	Socket Strip	(20) C13, (4) C19	24	Black		
EN2329	Enlogic	Intelligent PDU	Socket Strip	(24) C13, (8) C19	32	Black		

CatalogNumber	Product Family	Туре	Product Type	Socket Type	SocketQuantity	Color
EN2350	Enlogic	Intelligent PDU	Socket Strip	(20) C13/C15, (20) C13/C15/C19/C 21	40	Black
EN2380	Enlogic	Intelligent PDU	Socket Strip	(16) Locking C13/C15, (16) Locking C13/C15/C19/C	32	Black
EN2337	Enlogic	Intelligent PDU	Socket Strip	(38) C13, (6) C19	44	Black

	Table 2/5						
Catalog Number	Circuit Breaker	Switched Outlets	Circuit Breaker Quantity	Power Rating	Input Cable Location	Input Voltage	
EN2326	No Circuit Breaker	Yes	0	3.7 kVA	Top Feed	100 – 240V	
EN2316-A	16 A, 1-pole, Hy- Mag	Yes	0		Front Feed	100 – 240V	
EN2317	16 A, 1-pole, Hy- Mag	Yes	0		Top Feed	200 – 240V	
EN2325	16 A, 1-pole, Hy- Mag	Yes	2	7.4 kVA	Top Feed	200 – 240V	
EN2329	16 A, 1-pole, Hy- Mag	Yes	2	7.4 kVA	Top Feed	200 – 240V	
EN2350	20 A, 1-pole, Hy- Mag	Yes	2	7.4 kVA	Top Feed	200 – 240V	
EN2380	20 A, 1-pole, Hy- Mag	Yes	2	7.4 kVA	Top Feed	200 – 240V	
EN2337	16 A, 1-pole, Hy- Mag	Yes	2		Top Feed	200 – 240V	

	Table 3/5							
Catalog Number	Phase	Max Power Input	Nominal Voltage	On/Off Switch Included	Output Voltage	Amperage (Derated Amperage)		
EN2326	1 PH	3.68 kVA	230V	Yes	230VAC	16 A		
EN2316-A	1 PH	3.68 kVA			100 - 240VAC	20 A (16 A) North America, 16 A International		

CatalogNumber	Phase	Max Power Input	Nominal Voltage	On/Off Switch Included	Output Voltage	Amperage (Derated Amperage)
EN2317	1 PH	3.68 kVA			200 - 240VAC	16 A
EN2325	1 PH	7.44 kVA	230V	Yes	230VAC	32 A
EN2329	1 PH	7.44 kVA	230V	Yes	230VAC	32 A
EN2350	1 PH	7.44 kVA	230V	Yes	230VAC	32 A
EN2380	1 PH	7.44 kVA	230V	Yes	230VAC	32 A
EN2337	1 PH	7.44 kVA			200 – 240VAC	32 A

	Table 4/5							
Catalog Number	Plug Type	Rack Units	Removable Input Cable	Metering Type	Material	Finish		
EN2326	IEC 60309 316P6 (IP44)	OU	Yes	Input	Steel	Powder Coated		
EN2316-A	C20	OU	Yes	Input				
EN2317	IEC 60309 316P6 (IP44)	OU	No	Input				
EN2325	IEC 60309 332P6 (IP44)	OU	No	Input	Steel	Powder Coated		
EN2329	IEC 60309 332P6 (IP44)	OU	No	Input	Steel	Powder Coated		
EN2350	IEC 60309 332P6 (IP44)	OU	No	Input	Steel	Powder Coated		
EN2380	IEC 60309 332P6 (IP44)	OU	No	Input	Steel	Powder Coated		
EN2337	IEC 60309 332P6 (IP44)	OU	No	Input				

Table 5/5							
Catalog Number	Height	Width	Depth	Weight	Package Quantity	Interrupt Rating	

EN2326	58.66in	2.05in	2.09in	15.87lb	1	5kAIC
EN2316-A					1	5kAIC
EN2317					1	5kAIC
EN2325	68.9in	2.05in	2.09in	20.9lb	1	5kAIC
EN2329	68.9in	2.05in	2.09in	18.74lb	1	5kAIC
EN2350	58.66in	2.2in	2.95in	20.06lb	1	5kAIC
EN2380	58.66in	2.2in	2.95in		1	5kAIC
EN2337					1	5kAIC

## **ADDITIONAL PRODUCT DETAILS**

Please order bracket for vertical mounting separately.

## **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE