


Mobile Base for Open Frame Racks

Data Solutions



The Mobile Base for Open-Frame Racks provide stability and mobility to open-frame racks. It has models for both 19-in. 2- and 4-Post Open Frame Racks. This product mounts to the bottom of the racks previously mentioned. It includes four non-locking casters but will also accept standard levelers. Please note, catalog number PMBLM12 must be ordered separately, however the mounting hardware is included.

FEATURES

The Mobile Base for Open-Frame Racks provide stability and mobility to open-frame racks

It has models for both 19-in. 2- and 4-Post Open Frame Racks

This product mounts to the bottom of the racks previously mentioned. It includes four non-locking casters but will also accept standard levelers

Please note, catalog number PMBLM12 must be ordered separately, however the mounting hardware is included

SPECIFICATIONS

Table 1/1						
Catalog Number	Article Number	Material	Finish	Color	Color Code	Thickness
A19MB1000	13774	Mild Steel	Powder Coated	Jet Black	RAL 9005	12ga
A19MB600	13772	Mild Steel	Powder Coated	Jet Black	RAL 9005	12ga

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE