

Rail Web Mold Clamp, Adjustable

Data Solutions



FEATURES

Adjusts for a wide span of uses including frogs and switches

Lightweight and easy to use

Can also be used on standard (single) rail

SBC105RR provides improved safety with non-sharp profiles and reflecting tape for high visibility

SPECIFICATIONS

Table 1/1

Catalog Number	Welder Style	Mold Size	Jaw Opening
PBC105P1	T20	2 1/4"	24in max
SBC105RR	T21	2 3/8"	25.5in max
PBC105P	T20	3 1/2"	24in max
PBC105V	T20	3 1/2"	6in max
PBC105Q	T20	3 1/2"	6in max

Catalog Number	Welder Style	Mold Size	Jaw Opening
SBC105R	T21	3"	25.5in max
PBC105P2	T20	3"	24in max

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

 **WARNING:** This product can expose you to chemicals including diisononyl phthalate, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE