

RIM2-E Eave Panel

Data Solutions



nVent RAYCHEM RIM2-E panels are designed to mount on the roof eave and minimize the formation of icicles and ice dams during the winter season. RIM2-E panels embed 2 runs of energy efficient self-regulating heating cable in a specially designed base that directs most of the heat to the top surface for maximum efficiency. The base and heating cable are covered with cover panel which transfers heat along the continuous edge of the roof. The cover panels are available in variety of colors to match the roof material.

FEATURES

Prevents ice dam and icicle problems in eaves and valleys, avoids consequential roof damage

An aesthetically attractive solution, with no visible cables, various colors and finishes

Simple to install and operate

Energy efficient, self-regulating heating cable plus advanced UL and CSA Certified control systems

Reliable during long life: 20 year product warranty available

Maintenance free

SPECIFICATIONS

Heating Capacity: 16W/ft

Cable Type: Self-Regulating

Table 1/1

Catalog Number	Nominal Voltage	Color
F6237-AL-01-1	120V	Slate Gray
F6237-AL-01-2	240V	Slate Gray
F6237-AL-02-1	120V	Stone White

Catalog Number	Nominal Voltage	Color
F6237-AL-02-2	240V	Stone White
F6237-AL-03-1	120V	Bone White
F6237-AL-03-2	240V	Bone White
F6237-AL-04-1	120V	Almond
F6237-AL-04-2	240V	Almond
F6237-AL-05-1	120V	Sandstone
F6237-AL-05-2	240V	Sandstone
F6237-AL-06-1	120V	Sierra Tan
F6237-AL-06-2	240V	Sierra Tan
F6237-AL-07-1	120V	Teal
F6237-AL-07-2	240V	Teal
F6237-AL-08-1	120V	Regal Blue
F6237-AL-08-2	240V	Regal Blue
F6237-AL-09-1	120V	Sky Blue
F6237-AL-09-2	240V	Sky Blue
F6237-AL-10-1	120V	Sherwood Green
F6237-AL-10-2	240V	Sherwood Green
F6237-AL-11-1	120V	Hartford Green

Catalog Number	Nominal Voltage	Color
F6237-AL-11-2	240V	Hartford Green
F6237-AL-12-1	120V	Hemlock Green
F6237-AL-12-2	240V	Hemlock Green
F6237-AL-13-1	120V	Patina Green
F6237-AL-13-2	240V	Patina Green
F6237-AL-14-1	120V	Dark Ivy
F6237-AL-14-2	240V	Dark Ivy
F6237-AL-15-1	120V	Brandy Wine
F6237-AL-15-2	240V	Brandy Wine
F6237-AL-16-1	120V	Regal Red
F6237-AL-16-2	240V	Regal Red
F6237-AL-17-1	120V	Colonial Red
F6237-AL-17-2	240V	Colonial Red
F6237-AL-18-1	120V	Terra Cotta
F6237-AL-18-2	240V	Terra Cotta
F6237-AL-19-1	120V	Dark Bronze
F6237-AL-19-2	240V	Dark Bronze
F6237-AL-20-1	120V	Extra Dark Bronze

Catalog Number	Nominal Voltage	Color
F6237-AL-20-2	240V	Extra Dark Bronze
F6237-AL-21-1	120V	Mansard Brown
F6237-AL-21-2	240V	Mansard Brown
F6237-AL-22-1	120V	Medium Bronze
F6237-AL-22-2	240V	Medium Bronze
F6237-AL-23-1	120V	Matte Black
F6237-AL-23-2	240V	Matte Black
F6237-AL-24-1	120V	Classic Copper
F6237-AL-24-2	240V	Classic Copper
F6237-AL-25-1	120V	Silver Metallic
F6237-AL-25-2	240V	Silver Metallic
F6237-AL-26-1	120V	Champagne Metallic
F6237-AL-26-2	240V	Champagne Metallic
F6237-AL-27-1	120V	Cityscape
F6237-AL-27-2	240V	Cityscape
F6237-AL-28-1	120V	Charcoal Gray
F6237-AL-28-2	240V	Charcoal Gray
F6237-AL-29-1	120V	Tropical Patina

Catalog Number	Nominal Voltage	Color
F6237-AL-29-2	240V	Tropical Patina
F6237-AL-30-1	120V	Electric Blue
F6237-AL-30-2	240V	Electric Blue
F6237-AL-31-1	120V	Award Blue
F6237-AL-31-2	240V	Award Blue
F6237-AL-32-1	120V	Granite Green
F6237-AL-32-2	240V	Granite Green
F6237-CU-70-1	120V	Copper
F6237-CU-70-2	240V	Copper

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE