

# Spot Leak Detection Sensor

## Data Solutions



Spot Fluid Leak Sensor to detect punctual leak for nVent SCHROFF RackPower PDU's.

### FEATURES

Spot Fluid Leak Sensor to detect punctual leak

5 m Connection Cable

For RackPower RP1xxx, RP2xxx, RP6xxx Series PDU's

Hot pluggable for easy integration

Operating Temperature range 0 to 65 °C

Measuring Range < 2 MOHMS PER CM

### SPECIFICATIONS

Table 1/1

| Catalog Number | Works With | Height | Package Quantity | Plug Type | Removable Input Cable |
|----------------|------------|--------|------------------|-----------|-----------------------|
| EA9111         | RackPower  | 12.2in | 1                | RJ45      | No                    |

### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**