

Universal Restraint Clip, Slotted

Data Solutions



CERTIFICATIONS



FEATURES

Slotted design ideal for attaching to existing threaded rod on trapezes

Meets CEN/TS 17551:2021 requirements for Seismic Sway Bracing

SPECIFICATIONS

Finish: Electrogalvanized

Material: Steel

Table 1/1

Catalog Number	Brace Size	Rod Size (RS)	Thickness (T)
CSBURCR12	#12, #18	0.5in	0.17in
CSBURCR38	#12, #18	0.375in	0.17in


Catalog Number	Brace Size	Rod Size (RS)	Thickness (T)
CSBURCR58	#12, #18	0.625in	0.17in

ADDITIONAL PRODUCT DETAILS

Brace member is not included.

UL Loads		
Part Number	Brace Member	Load Rating
CSBURCR38	CSB12CBL	418 lb
	CSB18CBL	772 lb
CSBURCR12	CSB12CBL	418 lb
	CSB18CBL	772 lb
CSBURCR58	CSB12CBL	418 lb
	CSB18CBL	772 lb

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE