

# Varistar CP Server Cabinet With Castors

## Data Solutions



Welded steel frame for high dynamic load requirements.  
Prepared for 19" integration of IT assets.

### FEATURES

Preconfigured, ready to use cabinet

High dynamic load 1000 kg with integrated castors, static load-carrying capacity up to 1600 kg

Ingress protection class IP 20

Installation of different IT equipment possible

Integrated air panels for front to back cooling

Can be easily integrated into aisle containment system

### SPECIFICATIONS

<b>Product Type:</b>	Rack
<b>Cladding Color Code:</b>	RAL 7021
<b>Frame Material:</b>	Steel

Table 1/2

Catalog Number	Rack Height	Cladding Material	Cladding Color	Package Quantity	Dynamic Load	Finish
----------------	-------------	-------------------	----------------	------------------	--------------	--------

10630-021	42U	Steel	Black Grey	1	2200lbf	Powder Coated
10630-022	42U	Steel	Black Grey	1	2200lbf	Powder Coated

Table 2/2		
Catalog Number	Material	Type
10630-021	Steel	Mobile
10630-022	Steel	Mobile

### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE