

# **Aircraft Grounding Receptacle with Bar Attachment Point**



#### **CERTIFICATIONS**



## **FEATURES**

Castings for use in static grounding systems of refueling areas

Suitable as a combination tie down and static ground point

Easily connected to grounding system conductor and/or ground rods

Designed for simple installation with flush paved surfaces

Compatible with nVent ERICO Cadweld connections


# **SPECIFICATIONS**


**Material:** Phosphor Bronze

Table 1/1										
Catalog Number	Diameter 1 (Ø1)	Diameter 2 (Ø2)	Depth (D)	Attachment Point (AP)	Pipe Size	Connection Type				
B167	4 3/4"	4 13/32"	7 1/4"	1 1/2" Diameter Bar	1/2"	RA, RB				

CatalogNumber	Diameter 1(Ø1)	Diameter 2(Ø2)	Depth (D)	Attachment Point (AP)	Pipe Size	Connection Type
B166	3 7/8"	3 1/2"	5 1/4"	3/4" Diameter Bar	1/2"	RA, RB

### **DIAGRAMS**





## **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

<sup>△</sup> WARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

#### **North America**

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

# Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

#### Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

# APAC

Shanghai: + 86 21 2412 1618/19 Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE