

Arcweld Rail Bond, Power, Formed



FEATURES

Provides unchanging electrical resistance

Superior corrosion resistance

Includes ropelay copper cable for maximum flexibility

Highly durable

SPECIFICATIONS

Bond Terminal Style: AT


Finish: Bare;Copper Plated

Material: Copper;Steel

Table 1/1									
Catalog Number	Conductor Size	Length 1 (L1)	Length 2 (L2)	Height (H)	Diameter 1 (Ø1)	Diameter 2 (Ø2)			
PBAT13B002	300 kcmil Ropelay	17 3/4"	2 1/4"	5.13"	0.65"	0.44"			
PBAT12S10	4/0 Ropelay	8.44"	2 1/4"	2.69"	0.6"	0.44"			
PBAT13B003	300 kcmil Ropelay	15 3/4"	2 1/4"	5.63"	0.65"	0.44"			
PBAT12S7	4/0 Ropelay	6 3/4"	2 1/4"	3 1/4"	0.6"	0.44"			

CatalogNumber	Conductor Size	Length 1 (L1)	Length 2 (L2)	Height (H)	Diameter 1(Ø1)	Diameter 2(Ø2)
PBAT12J8	2/0 Ropelay	6.44"	2 1/4"	3"	0.47"	0.44"
PBAT12W10	250 kcmil Ropelay	8.44"	2 1/4"	3 1/4"	0.65"	0.44"

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE