

# Arcweld Rail Bond, Power, Straight



## FEATURES

Provides unchanging electrical resistance

Superior corrosion resistance

Includes ropelay copper cable for maximum flexibility

Highly durable

## SPECIFICATIONS

**Finish:** Bare;Copper Plated


**Material:** Copper;Steel

Table 1/1

Catalog Number	Conductor Size	Length (L)	Width (W)	Diameter 1 (Ø1)	Diameter 2 (Ø2)
PBAT23B90	300 kcmil Ropelay	90"	2 1/4"	0.71"	0.44"
PBAT23B46	300 kcmil Ropelay	46"	2 1/4"	0.71"	0.44"
PBAT23B28	300 kcmil Ropelay	28"	2 1/4"	0.71"	0.44"
PBAT23B20	300 kcmil Ropelay	20"	2 1/4"	0.71"	0.44"
PBAT23B22	300 kcmil Ropelay	22"	2 1/4"	0.71"	0.44"

## DIAGRAMS

---



## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**